

Ratings:

Current 16A
Voltage 300 V
Wire Size 28-14AWG
Test Voltage 2.0 kV

Rated Cross Section:



Single Wire (solid) 2.5mm²
Stranded Wire (flexible) 2.5mm²
Stranded Wire with Ferrules 1.5mm²

Dimensions:

Spacing 5.0mm (5.08mm)
PCB Hole Diameter 1.0mm (2x)
Stripped Length 6.0mm

Materials:

Insulating Material PA
Flammability UL94V-0
Temperature -30°C/+105°C
Tension Spring Stainless Steel
Contact Cu
Color Slade Gray



ON - SHORE TECHNOLOGY, INC.

Part Number

ED(Z)3101/[*][*]-WD

* - NUMBER OF POSITIONS

Units

mm

Drawing

Reviewed

Approved

Date

2/12/99

Sheet 1 of 1

Rev. A