


THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION
© COPYRIGHT 19 BY AMP INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHTS RESERVED. AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR PATENTS PENDING.



- 1 WIRE INSULATION DIA = SEE TABLE, DIM "A"
- 2 TONGUE MATERIAL THK. = .031 ± .002
- 3 BODY FINISH: TIN PLATE (MIL-T-10727) .000100 MIN THK.

OBSELETE
OBSELETE
OBSELETE

REVISIONS				
P	F	ZONE	LTR	DESCRIPTION
✓	✓	F		REDRAWN-REV PER G-1477, G-1175 #
✓	✓	G		PER-0095, -0096, -0099, -0100
✓	✓	H		OBSELETE - 54-G PER G-2393
✓	✓	I		REVISED - G-3049, -61
✓	✓	J		085-41-7 PER G-3793 & G-3794
✓	✓	K		REV PER G-5482
✓	✓	L		REV/0720-0049-93

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ON DECIMALS ± .0008 ANGLES		CONTRACT NO		NAME	
MATERIAL INSULATION: NYLON-BLUE		DR UTA /RFB 9-27-85		AMP	
SLEEVE: COPPER (Q-C-576)		CHK 1-27-86		AMP INCORPORATED	
BODY: PHOSPHOR BRONZE (Q-B-750)		APPO 1-27-86		Harrisburg, Pa.	
OTHER APPO		APPO		P.I.D.G, SPRING SPADE (SHORT)	
SCALE NTS		FSCM NO		DRAWING NO	
00779		52935		52935	
SHEET 1 OF 1					