








LOC		DIST		REVISIONS				
AJ		16		REV	DESCRIPTION	DATE	DWN	APVD
				AB	REVISED PER ECO-08-009474	7/21/2008	DW	JL
				AB1	REVISED PER ECO-09-021826	12SEP09	KK	AEG



- 1 POLYESTER, PBT, BLACK, PER MIL-M-24519.
- 2 POLYMETHYLPENTENE GENERAL PURPOSE.
- 3 ZINC PER QQ-Z-363.
- 4 PHOSPHOR BRONZE PER QQ-B-750.
- 5 BRASS PER QQ-B-626.
- 6 BRASS PER ASTM-B-453.
- 7 NICKEL PL PER QQ-N-290.
- 8 TIN PLATE PER ASTM-B-545.
- 9 TIN PLATE PER ASTM-B-545.
- 10 SELECTIVELY GOLD PLATED ON INTERFACE AREA PER MIL-G-45204, .000030 THK, TIN PLATED ON SOLDER TAIL PER ASTM-B-545, ALL OVER NICKEL PL PER QQ-N-290.
- 11 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



OBSOLETE	-	VIEW X	VIEW X	1000 pf, 2200 VDC	1-413515-1
	-	VIEW X OR Y	VIEW X	9400 pf, 1500 VDC	1-413515-0
SUPERCEDED BY 5413515-8	.110	VIEW Z	VIEW X	9400 pf, 1500 VDC	413515-9
	.185	VIEW Z	VIEW X	9400 pf, 1500 VDC	413515-8
SUPERCEDED BY 413515-7	.110	VIEW Z	VIEW X	7900 pf, 1600 VDC	413515-7
	.185	VIEW Z	VIEW X	7900 pf, 1600 VDC	413515-6
SUPERCEDED BY 413515-2	-	VIEW X OR Y	VIEW Y	9400 pf, 1500 VDC	413515-5
	-	VIEW X OR Y	VIEW Y	9400 pf, 1500 VDC	413515-4
SUPERCEDED BY 413515-2	-	VIEW X OR Y	VIEW X	20000 pf, 500 VDC	413515-3
	-	VIEW X OR Y	VIEW X	9400 pf, 1500 VDC	413515-2
SUPERCEDED BY 413515-2	-	VIEW X OR Y	VIEW X	9400 pf, 500 VDC	413515-1
	-	VIEW X OR Y	VIEW X	9400 pf, 500 VDC	413515-1
L		MOUNTING POST	CLIP	CAPACITANCE & VOLTAGE	PART NO

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN P. KERLIN CHK R. E. RUTH APVD P. BIRD	5/4/90 5/18/90 5/18/90	Tyco Electronics Corporation Middletown, PA 17057	
DIMENSIONS: INCHES		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME JACK, DECOUPLER, RIGHT ANGLE, LOW PROFILE, SERIES BNC	
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± .008 4 PLC ± - ANGLES ± -		PRODUCT SPEC 108-1269 APPLICATION SPEC		SIZE A1	
MATERIAL THRU 6		FINISH 7 8 9 10		RESTRICTED TO -	
CUSTOMER DRAWING		SCALE 4:1		SHEET 1 of 1	
				REV AB1	