

4600 and 4400 series

Toggle switches

Distinctive features and specifications

UG1410A



- ☐ High current/voltage rating in a small case
- ☐ Butt action contacts
- ☐ Insulated or metal lever
- ☐ UL, CSA and VDE (EN 61058-1) approved

ELECTRICAL SPECIFICATIONS

- Max. current/voltage rating with resistive load (silver contacts A) : 4A 250VAC - 6A 125VAC
- Approved electrical ratings : see table below
- Initial contact resistance : 10 mΩ max.
- Insulation resistance : 1.000 MΩ min. at 500VDC
- Dielectric strength :
 - 2.000 Vrms 50 Hz min. between terminals
 - 2.500 Vrms 50 Hz min. between poles and between terminals and frame
- Electrical life : 10.000 cycles at full load

APPROVALS	MODELS	POLES	FUNCTIONS	APPROVED RATINGS
UL/CSA	4600A	1-2	1-6-9	3A 250VAC - 6A 125VAC
VDE (EN 61058-1)	4400A	1-2	1-6	4(2)A 250VAC
	4600A	1-2-3	1-6	4(2)A 250VAC

MATERIALS

- Case : melamine phenolic
- Actuator :
 - insulated : polyamide ,6-6
 - non-insulated : brass, nickel plated
- Bushing :
 - insulated : polyamide 6-6
 - non-insulated : brass, nickel plated
- Contacts : silver

GENERAL SPECIFICATIONS

- Torque : 0,95 Nm (.70 Ft.lb) max. applied to nut
- Panel thickness : 5 mm (.196) between 2 nuts
- Operating temperature : -20°C to +55°C
- Hand soldering : 270°C max. for 10 seconds max. - iron Ø3 (.118)

AGENCY APPROVALS



EN 61058-1

Availability : see above chart.

Marking : VDE approved models are standard marked.



To order switches marked UL-CSA, complete appropriate box of ordering format.

The company reserves the right to change specifications without notice.

4600 and 4400 series

Toggle switches

Overview



ABOUT THIS SERIES

Dimensions : first dimensions are in mm while inches are shown as bracketed numbers.



NOTICE : please note that not all combinations of above numbers are available. Refer to the following pages for further information.



Sealing boots are available on 3 pole models to protect the switches against dust and water. They are presented in section H.



Mounting accessories : standard hardware supplied with all models : 1 hex nut U166 and 1 knurled nut U520 in the same colour as the lever (insulated models) or U411 nickel plated (metal lever models). Standard and special hardware available are presented in section I.



Packaging unit : 20 pieces.


4600 and 4400 series

Toggle switches


Insulated flat lever

MODEL
STRUCTURE

→ Keyway



- Solder lug/quick-connect terminals 2,8 x 0,5 (.110 x .019)
- Straight PC terminals or quick-connect terminals 4,7 x 0,8 (.185 x .031)
- 2 and 3 maintained positions
- 1 and 2 pole configurations



MODEL
STRUCTURE




Solder lug/quick-connect terminals - single pole

→ Keyway



4631 -2
4636 -2
4639 -2

III	II	I
ON	-	OFF
ON	-	ON
ON	OFF	ON




Solder lug/quick-connect terminals - double pole

→ Keyway



4641 -2
4646 -2
4649 -2

III	II	I
ON	-	OFF
ON	-	ON
ON	OFF	ON




Straight PC terminals - single pole

→ Keyway



4431 -2
4436 -2
4439 -2

III	II	I
ON	-	OFF
ON	-	ON
ON	OFF	ON



4600 and 4400 series

Toggle switches

Insulated flat lever



Straight PC terminals - double pole



4441 -2
4446 -2
4449 -2

III	II	I
ON	-	OFF
ON	-	ON
ON	OFF	ON

→ Keyway





Quick-connect terminals 4,7 x 0,8 (.185 x .031) - single pole




4631/8 -2
4636/8 -2

I		II
ON	-	OFF
ON	-	ON

→ Keyway



PANEL CUT-OUT




4600 and 4400 series

Toggle switches



Round lever - three pole

MODEL
STRUCTURE

→ Keyway



- Solder lug or straight PC terminals
- 2 and 3 maintained positions



MODEL
STRUCTURE





Solder lug terminals - metal lever

→ Keyway



4651
4656
4659

III	II	I
ON	-	OFF
ON	-	ON
ON	OFF	ON





Straight PC terminals - metal lever

→ Keyway



4451
4456
4459

III	II	I
ON	-	OFF
ON	-	ON
ON	OFF	ON





Solder lug terminals - insulated lever - silver contacts

→ Keyway



4651A-32
4656A-32

I	II
ON	-
ON	-
ON	ON






4600 and 4400 series

Toggle switches

CONTACT MATERIAL




ACTUATORS



- Blank** Round, metal lever for 3 pole only
- 2** Insulated flat lever (for single and double pole only)
- 32** Black insulated round lever (for 3 pole only)

ACTUATOR COLOURS




- 1** Blue
- 2** Black (standard)
- 3** Green
- 4** Grey
- 5** Yellow
- 6** Red
- 7/1** White
- 9** Orange



For insulated flat lever
Black : standard colour - reduced delivery time
Minimum order of 500 pieces for non-standard colours.

APPROVALS



UU (UL-CSA) Single and double pole only

Availability : see specifications for details of approved models.

Marking : to order switches marked UL-CSA, complete above box with 'UU'.
Other approvals available as standard, see specifications.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Apem:](#)

[4631A22UU](#) [4636A22UU](#) [4639A22UU](#) [4641A22UU](#) [4441C22](#) [4641A22](#) [4651A32](#) [4656A32](#)