

Search Results

- Evaluate
- FAQ's
- How to Buy
- Bill of Material
 - Favorite Products List
 - Locate Distributor

Home > Product On-Line Catalog > Search Results >

Current refinements (click  to remove) [Search Tips](#) 

 **Text Search: 'FZOPE3-10M5'**

Your search criteria matched only one product, shown below

FZOPE3-10M5



- Patch cords are tested to support network transmission speeds up to 10 Gb/s for link lengths up to 550 meters with an 850nm source per IEEE 802.3ae 10 GbE standard
 - Pass all TIA/EIA-568-B.3 performance requirements
 - Insertion loss per connection: 0.10dB typical; 0.30dB maximum
 - Backward compatible for use with all 50/125µm system requirements
 - Factory terminated and 100% tested for insertion loss
 - Insertion loss data recorded for every multimode patch cord
 - Lifetime traceability of test data to a Q.C. number on each patch cord
 - SC Duplex Patch Cords include SC Duplex Clips to maintain polarity
 - Highest quality flame retardant fiber optic cable with tight-buffered coating on each optical fiber
- *Additional lengths and availability: Patch cords are available in 1 – 10 meter lengths in 1 meter increments, and 15, 20, 25 and 30 meter lengths. Pigtails are available in 1, 2, and 3 meter lengths. Ex: To order lengths other than 1 meter, replace the 1 after the M (FZPE10-10M1) with the desired length (FZPE10-10M2 for 2 meter length). The above lengths are stock items. For

other lengths, contact Customer Service for actual lead times.

• Part Number	FZOPE3-10M5
• RoHS Compliancy Status	RoHS directive is not applicable
• Note	Intended for use in fixed installations which are outside the scope of RoHS
• Part Description	SC to LC Patch Cord, Optimized OM4, 0.15 dB IL Loss, Duplex, Plenum, 1.6mm jacketed cable – 5m.
• Product Type	Hybrid Patch Cords
• Length (m)	5
• Fiber Compatibility	10 GbE 50/125µ
• Fiber Cable Size	1.6mm
• Fiber Cable Type	Jacketed Cable
• Fiber Type	Multimode
• Connector 1 Type	SC Connector
• Connector 2 Type	LC Connector
• End Configurations	SC to LC
• Fiber Count	2
• Flammability Rating	Plenum (OFNP)
• Pricing Description	SC to LC, Optimized OM4, Duplex, Plenum, 1.6mm jacketed cable, 5M
• Min. Order UOM	PC
• Min. Order Qty.	1
• BOM Qty. (# of Pkgs.)	0
• Add to Favorite Product List	

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.