


REV.	DATE	DESCRIPTION
NC	05/11/04	UPDATE DRAWING FORMAT



					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007” .315 – 1.180 = ± 0.015” 1.180 – 4.724 = ± 0.020” DO NOT SCALE DRAWING	APPROVALS		DATE		Amphenol Connex									
8						DRAWN	G.R.S.	05/11/04											
7						CHECKED													
6						ISSUED				PART DESCRIPTION									
5	HEX NUT	BRASS	GOLD	1							SMB P.C.B. BULKHEAD RECEPT. JACK								
4	LOCK WASHER	BRASS	GOLD	1															
3	CONTACT PIN	BRASS	GOLD	1															
2	INSULATOR	TEFLON	NATURAL	1							PART NO.								
1	BODY	BRASS	GOLD	1						142204-75									
	DESCRIPTION	MATERIAL	FINISH	QTY						DWG. NO.		142204-75.DWG		REV.	NC	SIZE	A	SCALE	NA
										CAD FILE					C:/142/142204-75.DWG				