



		13		12		11		10		9		8		7		6		5		4		3		2		1			
J		PART NUMBER		ENGINEERING NUMBER		FINISH LENGTH																						J	
		1300060339		103000A06M020		6' 6" +3.50" -0 [2M +88.9 -0]																							
		1300060345		103000A06M050		16' 4" +6.50" -0 [5M +165.1 -0]																							
I		1300060353		103000A06M100		32' 4" +12.50" -0 [10M +317.5 -0]																						I	
		1300060356		103000A06M150		49' 2" +24.50" -0 [15M +622.3 -0]																							
		1300060359		103000A06M300		98' 4" +24.50" -0 [30M +622.3 -0]																							
H		<p>NOTE</p> <p>1) MATERIAL: SEE TABLE</p> <p>2) FINISHES: SEE TABLE</p> <p>3) WRAP LABEL IS MARKED WITH P/N, DATE CODE, VOLTAGE &amp; AMPERAGE</p> <p>4) MATES WITH: MINI CHANGE, 3 POLE RECEPTACLE</p> <p>5) ELECTRICAL DATA: INLINE CORDSET FEMALE A-SIZE WITH FLYING LEADS 18AWG UNSHIELDED POLES: 3 MAX. VOLTAGE: 300V MAX. CURRENT 7A PROTECTION IP67 TEMPERATURE RANGE: -20°C TO 105°C</p> <p>6) PACKAGING: CABLE ASSEMBLIES ARE BAGGED SEPERATELY IN POLY BAGS WITH BAR CODE LABEL ATTACHED TO OUTSIDE OF BAG.</p> <p>7)ASSEMBLY IS RoHS COMPLIANT.</p> <p>8)CERTIFICATION CSA CERTIFIED, FILE NO. LR6837</p>																										H	
G																												G	
F																												F	
E																												E	
D																												D	
C																												C	
B																												B	
A																												A	
		6		1		LABEL		PLASTIC FILM		BLACK/YELLOW		8		7		6		5		4		3		2		1			
		5		3		CONTACT SOCKET		COPPER ALLOY		GOLD PLATED		8		7		6		5		4		3		2		1			
		4		1		INSERT		PVC		YELLOW		8		7		6		5		4		3		2		1			
		3		1		COUPLING NUT		ZINC DIE CAST		BLACKE-COATED		8		7		6		5		4		3		2		1			
		2		1		OVERMOLD		PVC		YELLOW		8		7		6		5		4		3		2		1			
		1		1		CABLE, 18AWG-3		PVC		YELLOW		8		7		6		5		4		3		2		1			
		ITEM		QTY.		DESCRIPTION		MATERIAL		FINISH		8		7		6		5		4		3		2		1			
		13		12		11		10		9		8		7		6		5		4		3		2		1			