




FEATURES:

- Easy to assemble threaded two piece construction enables solderless wire attachment by means of an internal set screw
- Compatible with 18 to 22 AWG wire
- Banana plug spring is Beryllium Copper for long insertion life
- Banana plug body and spring are nickel plated for tarnish resistance

MATERIALS:

Plug Body: Brass, Nickel Plated

Plug Spring: Beryllium Copper, Nickel Plated

Insulation: Nylon

Set Screw: Brass

RATINGS:

Operating Voltage: 750V AC/DC (Independent of Wire)

Current: 25 Amperes Max

ORDERING INFORMATION: Model 5934-*

* = Color Code, Standard Colors: -0 Black, -2 Red

Sold in packages of 10 per color.

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).

All specifications are to the latest revisions. Specifications are subject to change without notice.

Registered trademarks are the property of their respective companies. Made in USA