

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

51191-1400

Status:

Active

Description:

2.50mm Pitch Wire-to-Wire and Wire-to-Board Receptacle Housing, with Guide Rails, 14 Circuits

Documents:

3D Model

Drawing (PDF)

Product Specification PS-51191-002 (PDF)

Product Specification PS-51191-003 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Application

Product Name

UPC

Crimp Housings

51191

Signal, Wire-to-Board, Wire-to-Wire

N/A

800753327948

Physical

Circuits (maximum)

Flammability

Gender

Glow-Wire Compliant

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Stackable

Temperature Range - Operating

14

94V-0

Female

No

Nylon

1304.100/mg

1

Bag

No

2.50mm

No

-40°C to +105°C

Material Info

Reference - Drawing Numbers

Product Specification

Sales Drawing

PS-51191-002, PS-51191-003, RPS-51191-007

SD-51191-004




image - Reference only

Series

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Low-Halogen Status

Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

51191Series

Mates With

5045 Vertical Header . 5046 Right Angle Header . 5240 Plug Housing

Use With

50802 Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION