

2589-ID-10

NOTES:

1. THESE MOUNTING CLIPS ARE FOR HOLDING THE 2481 SERIES HOUSINGS TO THE MAIN PANEL TOPS OF ELECTRIC RANGES.
2. SCREW SIZE INDICATION.
3. .015/(.38) MAXIMUM CUT OFF.
4. .010/(.25) MAXIMUM MISMATCH.
5. THREAD FORM FOR A #10-32 SCREW.
6. THIS SURFACE MAY BE FORMED IN THIS DIRECTION A MAXIMUM OF 5°.

MATERIAL:


STEEL, STAINLESS, TYPE 301, .020/(.5) THICK.

DIMENSIONS SHOWN (METRIC) INCH	
UNLESS OTHERWISE SPECIFIED TOLERANCES ANGULAR ± .006 5°	
3 PLACE	± .010
2 PLACE	± .014 ± 0.25
1 PLACE	± 0.35
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	
DRW'G. BY	RHR
CHK'D. BY	ESS
APP'D. BY	RAS
SCALE	2: 1

▽ = 0 ▽ = 0		REVISE ONLY ON CAD SYSTEM	
TITLE			
MOUNTING CLIP			
MOLEX INCORPORATED LISE,ILL. 60532 U.S.A.		SHEET NO. 1 of 3	DATE 11/20/92
PART NO. SEE SHEET 3		DRWG. NO. SD-2589-*	
FILE NAME SD2589X1	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		SIZE C


MFG. SH.	REV.	LTR.	REVISIONS
3	AB		
2	Z		
1	AC	X	

AC	OBSELETED P/N UCR2002-0255 01/9/12 COMERC
AB2	REMOVED NOTCH UCR2000-0104 8/11/99 COMERC
AB1	REV. RADII UCR2000-0086 8/05/99 COMERC
AB	REVISED UCR 1999-0818 6/03/99 ELHAG
AA	REVISED ECN U4 0744 6/16/94 RHR
Z	REVISED ECN U4 0213 2/14/94 RHR
Y	REVISED ECN U3 0739 5/13/93 RHR
X	REDRAWN & REDIM. ECN U2 1712 11/25/92 RHR





I3	I2	I1	I0	9	8	7	6	2589	4	3	2	I
----	----	----	----	---	---	---	---	------	---	---	---	---

	PART NO.	ENG. NO.	DIMENSION	
			A	
J	089-00-2006	2589-ID-10	.48±.025 (12.2±.64)	
	089-00-2022	2589-2C	.53±.025 (13.5±.64)	
	089-00-2025	2589-2H	.656±.025 (16.66±.64)	
I	089-00-2027	2589-2J-10	.562±.025 (14.27±.64)	
	089-00-2041	2589-3B	.48±.025 (12.2±.64)	
	089-00-2047	2589-6F	.375±.015 (9.53±.38)	
H	089-00-2100	2589-10C	.48±.025 (12.2±.64)	
	089-00-2101	2589-21A	.62±.025 (15.7±.64)	OBSOLETE
	089-00-2103	2589-23	.62±.025 (15.7±.64)	




FOR THE REMAINDER
OF DIMENSIONS AND
DETAILS SEE SHEET I

2589-23



FOR THE REMAINDER
OF DIMENSIONS AND
DETAILS SEE SHEET I

2589-21A OBSOLETE



				DIMENSIONS SHOWN (METRIC) INCH		▽ = 0 ▽ = 0		REVISE ONLY ON CAD SYSTEM														
AA SEE SHEET I				UNLESS OTHERWISE SPECIFIED TOLERANCES: ANGULAR ± 5° <table><thead><tr><th></th><th>INCH</th><th>METRIC</th></tr></thead><tbody><tr><td>3 PLACE</td><td>± .010</td><td>---</td></tr><tr><td>2 PLACE</td><td>± .014</td><td>± 0.25</td></tr><tr><td>1 PLACE</td><td>---</td><td>± 0.35</td></tr></tbody></table>			INCH	METRIC	3 PLACE	± .010	---	2 PLACE	± .014	± 0.25	1 PLACE	---	± 0.35	TITLE		MOUNTING CLIP		
	INCH	METRIC																				
3 PLACE	± .010	---																				
2 PLACE	± .014	± 0.25																				
1 PLACE	---	± 0.35																				
Z SEE SHEET I				MOLEX INCORPORATED		SHEET NO. 3	DATE 2/24/93															
AB SEE SHEET I				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		PART NO.		DRWG. NO.														
X SEE SHEET I				DRWG. BY: RHR CHK'D BY: ESS		SEE CHART		SD-2589-•														
LTR. REVISIONS		LTR. REVISIONS		APP'D BY: RAS SCALE 2: 1		FILE NAME: SD2589X3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INC. AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION.														
								DIV. CP	SIZE C													

I3	I2	I1	I0	9	8	7	6	5	4	3	2	I
----	----	----	----	---	---	---	---	---	---	---	---	---