

FLORSTAT SD STATIC DISSIPATIVE MATTING

Construction:

Double layer ESD

(conductive backing)

Thickness:

2mm

Form of supply:

Sheet - 2m width

Dimensional stability:

< 0.4% (DIN 16591)

Indentation:

< 0.05mm (DIN 51955)

Weight / sq m:

3.3 Kgm

Light fastness:

degree 7 (DIN 53388)

Sound absorption:

3 dB (DIN 52210)

Inflammability class:

B1 (DIN 4102)

Smoke emission class:

Q1

Electrical leakage resistance:

1 - 100 Megohm

(BS IEC 61340-4-1)

Colours:

9