



LOC	DIST	REV	DATE	APP
G	14			
		ZONE	LTR	
		B	REVISED PER 0720-0230-93	2/25/94



WIRE RANGE	E13288 Listed
16-14 AWG STRAINED	16-14 AWG STRAINED
LR7189 Certified	MILITARY P/N AND CLASS
NOT CERTIFIED	NOT APPLICABLE

△ STAMP AMP 16-14* APPROX AS SHOWN



AMP INCORPORATED CUSTOMER SERVICE SYSTEMS	MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111
FOR ORDER ENTRY	1-800-526-5142

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN - - - - - TOLERANCES ON - - 2 PLG DEC # - - 3 PLG DEC # - - ANGLES ± - -	DR 2-17-93 TA BRINKMAN	NAME
MATERIAL COPPER PER ASTM B-152 ANNEALED	CHK 2-17-93 DA PATTERSON	AMP Incorporated Harrisburg, PA 17105-3508
FINISH TIN PLATE 0.00254 [1.000100] MIN THK PER MIL-T-10727	APPO 2-17-93 DE MILLER	TERMINAL, SPADE TONGUE, BUDGET
APPLICATION SPEC	APPO 2-17-93 JL NECKLEY	SIZE CAGE CODE DRAWING NO 00779 C-33221
WEIGHT -	SCALE 10:1	SHEET 1 OF 1