



\*PARTS AVAILABLE BY SPECIAL ORDER ONLY

TO PRESS-FIT IN A  $.312 \pm .003$   
( $7.92 \pm 0.08$ ) DIA. HOLE, IN A  
.25 (6.4) MIN. THICK PANEL



M4 THREAD




\*BHEHCB


\*MSEHCB

### BASE STYLE

TO SNAP-LOCK IN A  
.187 $\pm$ .003 ( $4.75 \pm 0.08$ ) DIA.  
HOLE IN A .031-.078  
(0.79-1.98) PANEL  
THICKNESS




.25 (6.4)  
[.20 (5.2) -5 ONLY]




FOR #6 (M3.5),  
SELF TAPPING SCREW.

### HEAD STYLE




STANDARD NOSE  
STANDARD CLIP  
"C"=.29 (7.5)

-8  
STANDARD NOSE  
SHORT CLIP  
"C"=.24 (6.1)



-6  
SHORT NOSE  
SHORT CLIP  
"C"=.24 (6.1)

-7  
SHORT NOSE  
STANDARD CLIP  
"C"=.29 (7.5)



-9  
NO NOSE  
SHORT CLIP  
"C"=.24 (6.1)

-10  
NO NOSE  
STANDARD CLIP  
"C"=.29 (7.5)

EHCBS-A-01  
EHCBS-A-19

\*EHCBS-8-A-01  
\*EHCBS-8-A-19

\*EHCBS-6-A-01  
\*EHCBS-6-A-19

\*EHCBS-7-A-01  
\*EHCBS-7-A-19

\*EHCBS-9-A-01  
\*EHCBS-9-A-19

\*EHCBS-10-A-01  
\*EHCBS-10-A-19

\*TEHCB-A-01  
\*TEHCB-A-19

\*TEHCB-8-A-01  
\*TEHCB-8-A-19

\*TEHCB-6-A-01  
\*TEHCB-6-A-19


\*TEHCB-7-A-01  
\*TEHCB-7-A-19

\*TEHCB-9-A-01  
\*TEHCB-9-A-19

\*TEHCB-10-A-01  
\*TEHCB-10-A-19

SELECT BASE STYLE FROM LEFT TABLE COLUMN AND HEAD STYLE FROM THE TOP OF THE TABLE. WHERE THE COLUMN & ROWS INTERSECT IS THE CORRESPONDING PART NO.

TO FIT A  $.156 \pm .003$   
( $4.00 \pm 0.08$ ) DIA. HOLE, IN A  
.062 (1.57) THICK PC BOARD




TO SNAP-LOCK IN A  $.187 \pm .003$   
( $4.75 \pm 0.08$ ) DIA. HOLE IN A  
.031-.078 (0.79-1.98) PANEL THICKNESS

EXAMPLE:

EHCBS-7-6-01  
EHCBS-7-6-19  
PART NO. HEAD STYLE DIM. "A" MATERIAL

FOR DIMENSION "A" SEE CHART.




### NOTES:

1. MATERIAL: NYLON 6/6 (RMS-01),  
FLAME RETARDANT: NYLON (RMS-19),
2. COLOR: NATURAL.

\*\*ONLY TEHCB-4-01 OR "-19" AVAILABLE IN 1/4 (6.4) SIZE

| DIM. "A" | SIZE       |
|----------|------------|
| -4**     | 1/4 (6.4)  |
| -5       | 5/16 (7.9) |
| -6       | 3/8 (9.5)  |
| -8       | 1/2 (12.7) |
| -10      | 5/8 (15.9) |
| -12      | 3/4 (19.1) |
| -14      | 7/8 (22.2) |
| -16      | 1 (25.4)   |

TITLE: EDGE-HOLDING CIRCUIT BOARD SUPPORTS



|     |                             |             |
|-----|-----------------------------|-------------|
| I   | SEE CO 200035 FOR CHANGES   | SK 09.26.07 |
| H   | SEE ECN #1208 FOR CHANGES   | SK 11.29.06 |
| -   | SEE ENGINEERING FOR REV A-G | -           |
| REV | DESCRIPTION                 | ENGR DATE   |

|                                                                                |                                                      |                                                                                             |                                    |                     |
|--------------------------------------------------------------------------------|------------------------------------------------------|---------------------------------------------------------------------------------------------|------------------------------------|---------------------|
| TOLERANCES<br>UNLESS NOTED<br>.XX=±.010<br>.XXX=±.005<br>FRAC=±1/64<br>ANG=±1° | FILE # EHCBS<br>MAT'L: SEE NOTES<br>RE: RICHCO, INC. | DWN: S.M.<br>DT: 12/05/01<br>RICHCO INC.<br>PO BOX 804238, CHICAGO, 60680<br>(773) 539-4060 | APP:<br>DT:<br>PART #<br>SEE TABLE | PRINT<br>TYPE<br>CA |
|--------------------------------------------------------------------------------|------------------------------------------------------|---------------------------------------------------------------------------------------------|------------------------------------|---------------------|