

Tools



493791

Kit/Set	Description	Order Code	Price Each
Edge off EO 1000	Edge off consists of S10 non-removable blade mounted on a hexagon handle 125mm long	137-4051	
Rapid burr RB 1000	Rapid burr supplied with S10 blade. Will accept all S type blades	137-4063	
Noga burr 3	Noga burr 3 comes complete with S10, S20, S35 blades and is capable of holding all S type blades. For coarse and fine deburring	137-4071	
Noga burr 5	Noga burr 5 is similar to Noga burr 3 but is supplied with 5 blades S10/S20/S35/S101/S202	137-4073	
Double burr DB 1000	Double burr is a dual purpose tool for sheet metal. Adjustable up to 10mm thickness. Standard tool supplied with 2 N80 blades and hand guard for safety	137-4074	
Keyway burr KW 1000	Keyway burr for internal and external keyways, Tool length 236mm. Supplied with N80K blade	137-4075	
Tele burr LB 1000	Telescopic blade holder. Double ended taking heavy and light blades. Supplied with N1 and N2 blades	137-4076	
Leader LD 1000	Used to put chamfer on straight and curved components. Supplied with L1 blade	137-4077	
Scraper SC 1000	Supplied with T120 blade ground on both ends. Blade slides into handle and locks in any position	137-4078	
Medium scraper SC 8000	As above but supplied with T80 blade	137-4089	
Internal scraper IS	For deburring cross holes supplied with universal han-		

Internal scraper IS 1000	For deburring cross holes supplied with universal handle, D holder and D66 blade	137-4079
Countersink CS1000	Hexagon blade holder. Can be locked in any position. Complete with C20 90° countersink	137-4090
Roto-drive RD 1040	Roto-drive allows continuous rotation of tool. Supplied with fixed 8.3mm countersink	137-4091