




SECT. "A-A"



SECT. "B-B"

NOTE:

- 1. WIRE RANGE: AWG #24 ~ #28 (0.09 ~ 0.20 mm²)
- INSULATION RANGE: 0.1 ~ 2.4

GENERAL TOLERANCES	
10 UNDER	±0.2
10 OVER 30 UNDER	±0.25
30 OVER	±0.3
ANGLE	±3°

LOOSE	GOLD PLATING	08-70-1018	5009GL
CHAIN		08-70-1017	↑ G
LOOSE	PRE-TINNED	08-70-0051	↓ TL
CHAIN		08-70-0004	5009T
FORM	FINISH	EDP NO.	ENG. NO.

				公差 (Tolerances)		所要数 (Req)		DRWG.		
				.000 → ±0.005 .00 → ±0.05				DSN'D M. ENOMOTO 10/21/77		
				.0 → ±0.1 . → ±0.3				CHK'D K. S. Ima		
F	REVISED ECN. NO. 1045		10/12/79	K.H.			材料 (MAT'L) BRASS, 0.2t		APP'D	
E										
D	REVISED PER ECN 1078		1/24/79	MB						
C	REVISED PER ECN 912		8/4/78	MB	熱処理 (H.T.)		molex MOLEX-JAPAN CO., LTD. 日本モレックス株式会社			
B ₁	Revised Stopper		6/1/78	MB	HRe					
B	REMOVED X ECN NO. 748		3/18/78	MB						
A	REVISED		10/24/77	MB	仕上げ (Finish)		No.		SD-5009*	
O	PROPOSED		10/24/77	MB	SEE TABLE					
変更内容 (Rev.)		Date	Name	Scale	名称 (Name)					
				4	MINI-FIT				RECEPTACLE	

