



BS 88 - External front and side operation 20 to 160 A

Rating (A) Fuse size Frame size	Number of poles	Reference Switch I-O	Reference Changeover Switch I-O-II	External front handle I-O	TEST External front handle I-O TEST	External right side handle I-O	Changeover external front handle I-O-II	Shaft extensions for handle	Terminal shrouds ⁽¹⁾	Additional contact holder for U type AC	Integrated solid neutral link
20 A A1 0	3 P	3641 3000	3680 3000					320 mm 1401 0532		3999 0710 ⁽²⁾	
	3 P + switched neutral	3641 4000	3680 4000								
	3 P + solid neutral	3641 5000									
CD 32 A A1 0	3 P	3641 3001	3680 3001	Black S1 type IP55	Black S1 type IP65	Black S1 type IP55	Black S1 type IP55				
	3 P + switched neutral	3641 4001	3680 4001	1411 2111 ⁽³⁾	1413 2115 ⁽³⁾	1415 2111 ⁽³⁾	1411 2113 ⁽³⁾				
	3 P + solid neutral	3641 5001		Red/Yellow S1 type IP65	Red/Yellow S1 type IP65	Red/Yellow S1 type IP65	Red/Yellow S1 type IP65				
32 A A1 11	2 P	3841 2003		1414 2111	1414 2115	1418 2111	1414 2113		Standard		
	3 P	3841 3003	3880 3003								
	4 P	3841 6003	3880 6003								
63 A A2-A3 12	2 P	3841 2006									
	3 P	3841 3006	3880 3006								
	4 P	3841 6006	3880 6006								
100 A A4⁽⁴⁾ 13	2 P	3841 2010						320 mm 1400 1032		3999 0600 ⁽²⁾	3829 9310
	3 P	3841 3010	3880 3010								
	4 P	3841 6010	3880 6010								
CD 160 A A3-A4⁽⁴⁾ 13 A	2 P	3841 2014		Black S2 type IP55	Black S2 type IP65	Black S2 type IP55	Black S2 type IP55		2 P 3998 2016 3 P 3998 3016 4 P 3998 4016		
	3 P	3841 3014	3880 3014	1421 2111 ⁽³⁾	1423 2115 ⁽³⁾	1425 2111 ⁽³⁾	1421 2113 ⁽³⁾				
	4 P	3841 6014	3880 6014								
160 A A4 14	2 P	3841 2015		Red/Yellow S2 type IP65 1424 2111	Red/Yellow S2 type IP65 1424 2115	Red/Yellow S2 type IP65 1428 2111	Red/Yellow IP65 1424 2113				3829 9320
	3 P	3841 3015	3880 3015								
	4 P	3841 6015	3880 6015								
160 A B1-B2 14	2 P	3841 2016									
	3 P	3841 3016	3880 3016								
	4 P	3841 6016	3880 6016								

(1) Standard.

(2) 4 auxiliary contacts as standard without support (the support is for 4 additional auxiliary contacts).

(3) Top/bottom.

(4) For fuse size A4: max diameter 31 mm.