



Liquidtight Flexible Metal Conduit Fittings T&B Catalog Number:

5333SST

78621074480

Status:

Active

Description:

3/4 in. straight stainless steel liquidtight connector.

Features

Available in straight, 45 degree and 90 degree angled configurations to fit conduit from 3/8 in. to 2 in.

Application

Ideal for industrial MRO and OEM applications in food and beverage, pharmaceutical, petrochemical, wastewater, salt water and other corrosive environments.

Stronger and more UV-resistant than non-metallic fittings.

Rated for temperatures up to 105 degrees C (221 degree F)

Connects metallic-cored liquidtight conduit to a box or enclosure

General

Style	Insulated
Trade Size (inches)	3/4
Material	Stainless Steel
Working Temperatures	Up to 105 degree C (221 degree F)

Dimension Information

Dimension A (inches)	1.39
Dimension B (inches)	1.37

Specifications

3dmodel	Available on Website
---------	----------------------

Packaging

T&B Inner Pack	25
Package in Units	100
T&B Sold in UOM	Each
T&B Weight Per UOM	40 lbs. per 100

Application Support

304 Stainless Steel Corrosion Compatibility Chart	Available on Website
---	----------------------

T&B Sales Drawings	wsd-000171
Product Brochure	Available on Website

Certifications

RoHS Compliance	No
-----------------	----

Certifications



File Nbr:

E 23018

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com