

(1,27 mm) .050"

FTR SERIES

SMT MICRO HEADER

SPECIFICATIONS

For complete specifications and recommended PCB layouts see www.samtec.com/FTR

Insulator Material:

Black Liquid Crystal Polymer

Terminal Material:

Phosphor Bronze

Plating:

Au or Sn over

50µ" (1,27 µm) Ni

Current Rating:

1A per contact

Operating Temp Range:

-55°C to +105°C with Tin;

-55°C to +125°C with Gold

RoHS Compliant:

Yes

Processing:

Lead-Free Solderable:

Yes

SMT Lead Coplanarity:

(0,10 mm) .004" max (02-20)


(0,15 mm) .006" max (21-40)



Mates with:
RSM, SMS, SLM

OPTIONS

-P OPTION



Single and
double row

(2,54 mm)
.100"

Surface
Mount

Micro pitch
(1,27 mm) .050"

Available with optional
Pick & Place Pad

FTR

1

NO. PINS
PER ROWLEAD
STYLEPLATING
OPTIONROW
OPTION

OPTION

02 thru 40

Specify
LEAD
STYLE
from
chart

-L
= 10µ" (0,25 µm)
Gold on post,
Matte Tin on tail

-G
= 10µ" (0,25 µm)
Gold on post,
Gold flash on tail

Note: Other Gold plating
options available.
Contact Samtec.

-S
= Single
Row

-D
= Double
Row



- "XX"
= Polarized

-A
= Alignment Pin
(5 positions
minimum -D only)
(Metal or plastic at
Samtec discretion)
(N/A with -LC)


-LC
= Locking Clip
(6 positions
minimum -D only)
(N/A with -A)
(Manual placement
required)

-P
= Plastic Pick
& Place Pad
(-D = 5 positions
minimum)
(-S = 8 positions
minimum)




-TR
= Tape & Reel
(-S = 4 positions
minimum)




-P OPTION




-P OPTION




-S OPTION



-D OPTION



-A OPTION



-LC OPTION

Note: Some sizes, styles and
options are non-standard,
non-returnable.

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

SAMTEC USA • Tel: 1-800-SAMTEC-9 or 812-944-6733 SAMTEC NORTHERN CALIFORNIA • Tel: 408-395-5900 SAMTEC SOUTHERN CALIFORNIA • Tel: 1-800-726-8329
SAMTEC AMERICA LATINA COMERCIO EXTERIOR LTDA • Tel: (+55 31) 3786 3227 SAMTEC UNITED KINGDOM • Tel: 44 01236 739292 SAMTEC GERMANY • Tel: +49 (0) 89 / 89460-0
SAMTEC FRANCE • Tel: 33 01 60 95 06 60 SAMTEC ITALY • Tel: 39 039 6890337 SAMTEC NORDIC/BALTIC • Tel: +46-84477280 SAMTEC BENELUX • Tel: 44 01236 739292
SAMTEC ISRAEL • Tel: 972-3-7526600 SAMTEC INDIA • Tel: +91-80-3272 1612 SAMTEC ASIA PACIFIC • Tel: 65 6745-5955 SAMTEC JAPAN • Tel: 045-475-1385 SAMTEC CHINA • Tel: 86-21-6083 3766
SAMTEC TAIWAN • Tel: 886-2-2735-6109 SAMTEC HONG KONG • Tel: 852-26904858 SAMTEC KOREA • Tel: 82-31-717-5685 SAMTEC ANZ • Tel: 613 9580 0683