

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0003092049

Status:


Active

Overview:

Standard .093"

Description:

2.36mm (.093") Diameter Standard .093 Pin and Socket Plug Housing, 4 Circuits, Dual Row



Documents:	
3D Model	Product Specification PS-02-09 (PDF)
Drawing (PDF)	Product Specification PS-43660-9999 (PDF)
Packaging Specification (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	2163
Comments	14.0A max. can be achieved when housing is used with 42477 or 42478 terminals
Overview	Standard .093"
Product Name	Standard .093"
Physical	
Circuits (maximum)	4
Circuits Detail	(2 x 2)
Color - Resin	Natural
Flammability	94V-2
Gender	Dual
Glow-Wire Compliant	No
Material - Resin	Nylon
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface (in)	0.198 In
Pitch - Mating Interface (mm)	5.03 mm
Stackable	No
Temperature Range - Operating	-40°C to +105°C
Electrical	
CSA	LR19980
Current - Maximum	11A
UL	E29179
Material Info	
Old Part Number	2163-P1
Reference - Drawing Numbers	
Product Specification	PS-02-09, PS-43660-9999
Sales Drawing	SD-2163-*

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Contains SVHC: No

Halogen-Free

Status

Not Reviewed

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com

For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

2163Series

Mates With

2163r

Use With

1189 Crimp Terminals, 1190 Crimp Terminals, 1376 Male PC Tail Terminals, 1377 Female PC Tail Terminals, 1380 Male Crimp Terminals, 1381 Female Crimp Terminals, 1433 Crimp Terminals, 1434 Male Crimp Terminals, 1973 , 2151 , 2273 , 2870 , 2871 , 4272 , 4550 , 6271 , 6310 , 42477 , 42478

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION