







REVISIONS					
P	LTR	DESCRIPTION		DATE	APVD
	A	RELEASED	ECR-16-004636	15DEC12	T.Q W.H



3 Pos.

2 Pos.





4~15 Pos.

NOTES:

- 1.MATERIAL: HOUSING — NYLON 66 (UL94V-0)
POST — TIN BRASS
- 2.THIS PRODUCT IS "NO-KINK" VERSION OF P/N 292253
- 3.MATING RECEPTACLE P/N 173977
- 4.OBSOLETED RED COLOR PARTS.

						15	28	31.8	25.2	31.0
						14	26	29.8	23.2	29.0
						13	24	27.8	21.2	27.0
	9-292143-2	7-292143-2	5-292143-2	3-292143-2	1-292143-2	12	22	25.8	19.2	25.0
	9- -1	7- -1	5- -1	3- -1	1- -1	11	20	23.8	17.2	23.0
	9- -0	7- -0	5- -0	3- -0	1- -0	10	18	21.8	15.2	21.0
	8- -9	6- -9	4- -9	2- -9	-9	9	16	19.8	13.2	19.0
	8- -8	6- -8	4- -8	2- -8	-8	8	14	17.8	11.2	17.0
	8- -7	6- -7	4- -7	2- -7	-7	7	12	15.8	9.2	15.0
	8- -6	6- -6	4- -6	2- -6	-6	6	10	13.8	7.2	13.0
8- -5	6- -5	4- -5	2- -5	-5	5	8	11.8	5.2	11.0	
8- -4	6- -4	4- -4	2- -4	-4	4	6	9.8	3.2	9.0	
8- -3	6- -3	4- -3	2- -3	-3	3	4	7.8	¾	7.0	
8-292143-2	6-292143-2	4-292143-2	2-292143-2	292143-2	2	2	5.8	¾	5.0	
RED	BLACK	YELLOW	BLUE	NATURAL	Pos.	A	B	C	D	
PART NO.										

PART NO.



RECOMMENDABLE PCB LAYOUT
(PCB THK:0.8-1.6)

TOLERANCES UNLESS OTHERWISE SPECIFIED:		
10 ≥ *	:	±0.2
30 ≥ * > 10	:	±0.25
100 ≥ * > 30	:	±0.3
ANGLE	:	±3°

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± -
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
MATERIAL SEE NOTE	ANGLES FINISH ± - SEE NOTE

DWN S.XU	31JAN03	TE Connectivity			
CHK S.YAO	31JAN03				
APVD T. SASAKI	31JAN03	NAME POST HEADER ASS'Y HORIZONTAL TYPE (AMP CT CONNECTOR 2mm PITCH)			
PRODUCT SPEC 108-60016		SIZE A3			
APPLICATION SPEC —		CAGE CODE 00779		DRAWING NO C-292143	
WEIGHT 0.000000		RESTRICTED TO —		SCALE 5:1	
CUSTOMER DRAWING		SHEET 1 OF 1		REV A	