

THIS DRAWING IS UNPUBLISHED
VERTRAULICHE UNVERÖFFENTLICHE ZEICHNUNGRELEASE FOR PUBLIKATION
FREI FÜR VERÖFFENTLICHUNG

,2000

MATED WITH:
PASSEND ZU:

1104701

LOC
AIDIST
-REVISIONS
ÄNDERUNGEN

P

LTR

DESCRIPTION
BESCHREIBUNG

DATE

DWN

APVD

COPYRIGHT 2000

BY AMP INCORPORATED

ALL RIGHTS RESERVED
ALLE RECHTE VORBEHALTENPROJEKT NR.
EGGMN04419


B3

ECR-17-014051


04APR18

SG

MKO

CONTACT ARRANGEMENT
VIEW FROM CONECTING SIDE




A (2:1)

HMX.4/0.BU.S
0-1104700-1
80A 690V 6kV 3

(1:1)

NOTES

- 1 POWER CONTACT: 1 TO 4
OUTER DIMENSIONS OF INSULATION: MAX. Ø10,8 MM
- 2 SIGNAL CONTACT: 11 and 12
OUTER DIMENSIONS OF INSULATION: MAX.Ø4,8 MM
- 3 GROUNDING CONTACT:
- 4 SUITABLE HOOD SIZE 6: SERIES HB; HD; EMV AND HIP
- 5 STANDARDS:
DIN EN 61984; DIN EN 60664-1
- 6 UL; CSA AUTHORISATION
- 7 PACKAGING:
5 PIECES IN A CARTON

PN 0-1 AS SHOWN—
ORDERING TEXT: HMX.4/0.BU.S**SUPERSEDED BY**
T2100042201-000CONTACT ARRANGEMENT
VIEW FROM TERMINATION SIDE* DISTANCE FOR GUARANTEED
CONTACT MAX. 21 mmPANET CUT-OUT CONTACT INSERT
WHEN USED WITHOUT HOUSING

1	SCREW	STEEL	NICKEL PLATED	BLUE	DIN EN ISO 1207-M5X8	7
4	FIXING SCREW	STEEL	NICKEL PLATED	BLUE	M3X10,5	6
2	SOCKET GROUNDING CONTACT	BRASS	NICKEL PLATED	BLUE	-	5
1	CLAMP TAB	STEEL	NICKEL PLATED	BLUE	---	4
4	SOCKET CONTACT	BRASS	SILVER PLATED	BLUE	-	3
4	THREAD PIN	STEEL	NICKEL PLATED	BLUE	-	2
1	FEMALE INSERT	PBT-GF30	-	LIGHT GREY	-	1
QTY.	DESCRIPTION	MATERIAL	SURFACE	COLOR	NOTE	ITEM

PARTS LIST

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION. DIESES ZEICHNUNGSDOKUMENT WIRD DURCH AMP INCORPORATED KONTROLLIERT. ÄNDERUNGEN, DIE DEM TECHNISCHEN FORTSCHRITT DIENEN, SIND VORBEHALTEN. DEN JEWEILS LETZTGÜLTIGEN ÄNDERUNGSSTAND ERFAHREN SIE AUF ANFRAGE.		DWN SCHNEIDER 12.07.2005	 TE Connectivity			
DIMENSIONS: DIMENSIONEN: mm		CHK T. SCHNURPFEL 12.07.2005				
		APVD -	NAME FEMALE INSERT HMX.4/0.BU.S			
		PRODUCT SPEC. PRODUKTSPEZ. 108-74058	SIZE A3			
TOLERANCES UNLESS OTHERWISE SPECIFIED: ALLGEMEINTOLERANZEN n. ISO 8015 - n. ISO 2768 - mH-E n. DIN 16901- 140 0 PLC # 1 PLC # 2 PLC # 3 PLC # ANGLES / WINKEL #		APPLICATION SPEC. VERARBEITUNGSSPEZ. 114-74058	CAGE CODE 00779	DRAWING NO ZEICHNUNGS-NR. C=1104700		RESTRICTED TO NUR FUER
MATERIAL		WEIGHT GEWICHT 0,121 KG	CUSTOMER DRAWING / KUNDENZEICHNUNG			
FINISH / OBERFLAECHE / FARBE		SCALE MASSSTAB 1:1		SHEET BLATT 1	OF VON 1	REV. B3