


4

3

2

1

UNIT: mm




CABLE WHITE PRINT


USB CABLE E189529 24AWG/2C 80°C 30V VW-1

Electrical test:

- 1. 100% short, open, miswire test
- 2. Conduct resistance: 2.0Ω (max)
- 3. Insulation resistance: $5M\Omega$ (min)
- 4. dielectric test: DC 300V



PIN ASSIGNMENT:



⑥	PE BAG	1/10	CLEAR SIZE: 280*330*0.05mm PRINT BLACK "MADE IN CHINA" + "10PCS".
⑤	PE BAG	1	CLEAR SIZE: 130*230*0.05mm PRINT BLACK "MADE IN CHINA" + "1PC".
④	TIE	2	BLACK L=100mm
③	OUT JACKET	6g	BLACK PVC-40P (MOULD NO.: WM-40)
②	CABLE	1	BLACK USB1.1 UL2725 28#/1P+24#/2C+AEB OD: 4.7mm L=2000±10
①	CONN	1	USB A MALE NICKEL PIN G/F 3PCS TYPE
NO.	NAME	Q'TY	SPECIFICATION

CNC Tech, LLC
Industrial Cable and Connector Technology

DRAWN	Andy	DRAWING NO	
CHECKED		CUSTOMER	
APPROVAL		ITEM NO.	101-1023-BL-00200
DECIDED		DATE	2013-8-23
VERSIONS/EDITION	A/0	PROJECTION	