




MSTBW 2,5/...-G


Open-end header
with stand-off

Pitch 5.0 or 5.08

Connection data

Further technical data see page 222.

I U
[A] [V]
12 250



MSTBA 2,5/...-G


Header with side panels,
plug-in direction **parallel** to the p.c.b.

Pitch 5.0 or 5.08

Connection data

Further technical data see page 222.

I U
[A] [V]
12 250



MSTB 2,5/...-GF

Header with screw flange,
plug-in direction **parallel** to the p.c.b.

Pitch 5.0 or 5.08

Connection data

Further technical data see page 222.

I U
[A] [V]
12 250



Type	Order No.	Pcs. Pkt.
MSTBW 2.5/2-G	17 36 11 1	50
MSTBW 2.5/3-G	17 36 13 8	
MSTBW 2.5/4-G	17 36 09 8	
MSTBW 2.5/5-G	17 36 08 5	
MSTBW 2.5/6-G	17 36 07 2	
MSTBW 2.5/7-G	17 36 06 9	
MSTBW 2.5/8-G	17 36 05 6	
MSTBW 2.5/9-G	17 36 04 3	
MSTBW 2.5/10-G	17 36 03 0	
MSTBW 2.5/11-G	17 36 02 7	
MSTBW 2.5/12-G	17 36 01 4	
MSTBW 2.5/13-G	17 36 00 1	
MSTBW 2.5/14-G	17 35 99 2	
MSTBW 2.5/15-G	17 35 98 9	
MSTBW 2.5/16-G	17 35 97 6	
MSTBW 2.5/17-G	17 35 96 3	
MSTBW 2.5/18-G	17 35 95 0	50
MSTBW 2.5/19-G	17 35 94 7	
MSTBW 2.5/20-G	17 35 93 4	
MSTBW 2.5/21-G	17 35 92 1	
MSTBW 2.5/22-G	17 35 91 8	
MSTBW 2.5/23-G	17 35 90 5	
MSTBW 2.5/24-G	17 35 89 5	

MSTBW 2.5/2-G-5.08	17 35 88 2	50
MSTBW 2.5/3-G-5.08	17 35 87 9	
MSTBW 2.5/4-G-5.08	17 35 86 6	
MSTBW 2.5/5-G-5.08	17 35 85 3	
MSTBW 2.5/6-G-5.08	17 35 84 0	
MSTBW 2.5/7-G-5.08	17 35 83 7	
MSTBW 2.5/8-G-5.08	17 35 82 4	
MSTBW 2.5/9-G-5.08	17 35 81 1	
MSTBW 2.5/10-G-5.08	17 35 80 8	
MSTBW 2.5/11-G-5.08	17 35 79 8	
MSTBW 2.5/12-G-5.08	17 35 78 5	
MSTBW 2.5/13-G-5.08	17 35 77 2	
MSTBW 2.5/14-G-5.08	17 35 76 9	
MSTBW 2.5/15-G-5.08	17 35 75 6	
MSTBW 2.5/16-G-5.08	17 35 74 3	
MSTBW 2.5/17-G-5.08	17 35 73 0	50
MSTBW 2.5/18-G-5.08	17 35 72 7	
MSTBW 2.5/19-G-5.08	17 35 71 4	
MSTBW 2.5/20-G-5.08	17 35 70 1	
MSTBW 2.5/21-G-5.08	17 35 69 1	
MSTBW 2.5/22-G-5.08	17 35 68 8	
MSTBW 2.5/23-G-5.08	17 35 67 5	
MSTBW 2.5/24-G-5.08	17 35 66 2	



Type	Order No.	Pcs. Pkt.
MSTBA 2.5/2-G	17 57 47 5	50
MSTBA 2.5/3-G	17 57 48 8	
MSTBA 2.5/4-G	17 57 49 1	
MSTBA 2.5/5-G	17 57 50 1	
MSTBA 2.5/6-G	17 57 51 4	
MSTBA 2.5/7-G	17 55 49 3	
MSTBA 2.5/8-G	17 57 52 7	
MSTBA 2.5/9-G	17 57 53 0	
MSTBA 2.5/10-G	17 57 54 3	
MSTBA 2.5/11-G	17 57 55 6	
MSTBA 2.5/12-G	17 57 56 9	
MSTBA 2.5/13-G	17 57 57 2	
MSTBA 2.5/14-G	17 57 58 5	
MSTBA 2.5/15-G	17 57 59 8	
MSTBA 2.5/16-G	17 57 60 8	50
MSTBA 2.5/17-G	17 57 61 1	
MSTBA 2.5/18-G	17 57 62 4	
MSTBA 2.5/19-G	17 57 63 7	
MSTBA 2.5/20-G	17 57 64 0	
MSTBA 2.5/21-G	17 57 65 3	
MSTBA 2.5/22-G	17 57 66 6	
MSTBA 2.5/23-G	17 57 67 9	
MSTBA 2.5/24-G	17 57 68 2	

MSTBA 2.5/2-G-5.08	17 57 24 2	50
MSTBA 2.5/3-G-5.08	17 57 25 5	
MSTBA 2.5/4-G-5.08	17 57 26 8	
MSTBA 2.5/5-G-5.08	17 57 27 1	
MSTBA 2.5/6-G-5.08	17 57 28 4	
MSTBA 2.5/7-G-5.08	17 57 29 7	
MSTBA 2.5/8-G-5.08	17 57 30 7	
MSTBA 2.5/9-G-5.08	17 57 31 0	
MSTBA 2.5/10-G-5.08	17 57 32 3	
MSTBA 2.5/11-G-5.08	17 57 33 6	
MSTBA 2.5/12-G-5.08	17 57 34 9	
MSTBA 2.5/13-G-5.08	17 57 35 2	
MSTBA 2.5/14-G-5.08	17 57 36 5	
MSTBA 2.5/15-G-5.08	17 57 37 8	
MSTBA 2.5/16-G-5.08	17 57 38 1	50
MSTBA 2.5/17-G-5.08	17 57 39 4	
MSTBA 2.5/18-G-5.08	17 57 40 4	
MSTBA 2.5/19-G-5.08	17 57 41 7	
MSTBA 2.5/20-G-5.08	17 57 42 0	
MSTBA 2.5/21-G-5.08	17 57 43 3	
MSTBA 2.5/22-G-5.08	17 57 44 6	
MSTBA 2.5/23-G-5.08	17 57 45 9	
MSTBA 2.5/24-G-5.08	17 57 46 2	



Type	Order No.	Pcs. Pkt.
MSTB 2.5/2-GF	17 76 69 2	50
MSTB 2.5/3-GF	17 76 70 2	
MSTB 2.5/4-GF	17 76 71 5	
MSTB 2.5/5-GF	17 76 72 8	
MSTB 2.5/6-GF	17 76 73 1	
MSTB 2.5/7-GF	17 76 74 4	
MSTB 2.5/8-GF	17 76 75 7	
MSTB 2.5/9-GF	17 76 76 0	
MSTB 2.5/10-GF	17 76 77 3	
MSTB 2.5/11-GF	17 76 78 6	
MSTB 2.5/12-GF	17 76 79 9	
MSTB 2.5/13-GF	17 76 80 9	
MSTB 2.5/14-GF	17 76 81 2	
MSTB 2.5/15-GF	17 76 82 5	
MSTB 2.5/16-GF	17 76 83 8	50
MSTB 2.5/17-GF	17 76 84 1	
MSTB 2.5/18-GF	17 76 85 4	
MSTB 2.5/19-GF	17 76 86 7	
MSTB 2.5/20-GF	17 76 87 0	

MSTB 2.5/2-GF-5.08	17 76 50 8	50
MSTB 2.5/3-GF-5.08	17 76 51 1	
MSTB 2.5/4-GF-5.08	17 76 52 4	
MSTB 2.5/5-GF-5.08	17 76 53 7	
MSTB 2.5/6-GF-5.08	17 76 54 0	
MSTB 2.5/7-GF-5.08	17 76 55 3	
MSTB 2.5/8-GF-5.08	17 76 56 6	
MSTB 2.5/9-GF-5.08	17 76 57 9	
MSTB 2.5/10-GF-5.08	17 76 58 2	
MSTB 2.5/11-GF-5.08	17 76 59 5	
MSTB 2.5/12-GF-5.08	17 76 60 5	
MSTB 2.5/13-GF-5.08	17 76 61 8	
MSTB 2.5/14-GF-5.08	17 76 62 1	
MSTB 2.5/15-GF-5.08	17 76 63 4	
MSTB 2.5/16-GF-5.08	17 76 64 7	
MSTB 2.5/17-GF-5.08	17 76 65 0	50
MSTB 2.5/18-GF-5.08	17 76 66 3	
MSTB 2.5/19-GF-5.08	17 76 67 6	
MSTB 2.5/20-GF-5.08	17 76 68 9	

