

- FAQ's

How to Buy

- Bill of Material
- Favorite Products List
- Locate Distributor

Current refinements (click to remove) Search Tips

❌ Text Search: 'FXLE10D-10M10'

Your search criteria matched only one product, shown below

- Colour -specific keys mechanically and visually distinguish connections to prevent positive and negative unintentional insertion into unlike keyed or non -keyed ports and allows design flexibility and versatility for a more discrete network
 - Factory terminated and 100% tested for insertion loss (all) and return loss (10Gig™ and SM).
- Assures high performance for increased up -time and lower cost of ownership
- Low smoke zero halogen meets IEC -60332 (LSZH) flame rating for standard compliant safety
 - Singlemode endfaces UPC polished (55dB min. return loss) ensures a high quality endface for higher return loss to meet application requirements
 - Every singlemode endface is 100% factory inspected in compliance with Telcordia GR -326-CORE, Issue 3 requirements to assure high performance
 - Keyed LC 10Gig™ Patch Cords and Pigtails are tested per IEEE 802.3ae 10 GbE to support network transmission speeds up to 10Gb/s for link lengths up to 300 meters for OM3 at 850nm to assure high performance and reliability
 - Test data supplied with each patch cord and pigtail establishes a performance reference to

streamline maintenance and troubleshooting

Additional lengths and availability: Keyed LC patch cords and pigtails are available in 1m – 10m lengths in 1m increments, and 15m, 20m, and 30m lengths. For other lengths, contact Customer Service for actual lead times.

Additional keyed colors include the following: G– Violet, H– Aqua, J– Rose, K– Slate, L– Brown, P– White, Q– Charcoal, R– Lavender, S– Peach, T– Steel Blue, V– Maroon and W– Mint.

Part Number	FXLE10D10M10
RoHS Compliancy Status	RoHS directive is not applicable
Note	Intended for use in fixed installations which are outside the scope of RoHS
Part Description	LC (keyed D- yellow) to LC multimode duplex patch cord LSZH,10 GbE, 1.6mm jacketed cable (one duplex keyed LC connector on one end and one duplex LC connector on the other end) – 50/125μ m
Product Type	Keyed LC LSZH Patch Cords
Length (m)	10
Fiber Compatibility	10 GbE 50/125μ m
Fiber Cable Size	1.6mm
Fiber Cable Type	Jacketed
Connector 1 Type	LC Connector - Keyed D (Yellow)
Connector 2 Type	LC Connector
Flammability Rating	Low Smoke Zero Halogen (LSZH)
Key Type and Color	Keyed D - Yellow
Pricing Description	Keyed LC (D-Yellow) to LC, 10GIG, Duplex, LSZH,10M
Min. Order UOM	PC
Min. Order Qty.	1
BOM Qty. (# of Pkgs.)	0
Add to Favorite Product List	€

Please [register](#) to utilize the 'Bill of Materials', 'Submit Quotes' and 'Favorite Product List' features.