



Sample photo

Order symbol: PCM 200/150 G
Product nbr: 6016329
Description: Enclosure, PC
Remarks: Grey cover

EAN:	6418074038166
El. number:	
Finland:	3421654
Denmark:	8212027381
Italy:	7341080
Sweden:	2535351
Norway:	2535537

Including: Base with metric knock-outs and TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:		Length	Width	Height	Rating:
mm:	255	180	150	Ingress Protection (EN 60529): IP 66/67	
inch:	10.0	7.1	5.9	Impact Resistance (EN 62262): IK 08	
Electrical insulation: Totally insulated					
Halogen free (DIN/VDE 0472, Part 815): Yes					
UV resistance: UL 508					
Flammability Rating (UL 746 C 5): UL 746C 5V					
Glow Wire Test (IEC 695-2-1) °C: 960					
NEMA Class: NEMA 1, 4, 4X, 6, 12, 13					
Certificates:					
Germanischer Lloyd (GL)					
Underwriters Laboratories					
Det Norske Veritas					
Fimko					
Europe EN 62208: 2003					
UL Canada					
Gost R					
Materials:					
Material:	Polycarbonate				
Base colour:	RAL 7035				
Cover colour:	RAL 7035				
Cover screws material:	Polyamide				
Cover screws colour:	Grey				
Gasket material:	TPE				
Temperatures:					
Short term:	-40 ... 120 °C				
Continuous:	-40 ... 80 °C				
Short term:	-40 ... 250 °F				
Continuous:	-40 ... 175 °F				
Accessories:					
MIV 200	Mounting plate (Galvanized steel)				
MIN 15	DIN-15 Mounting rail				
MIN 20	DIN-15 Mounting rail				
MIV 15	DIN-35 Mounting rail				
MIV 20	DIN-35 Mounting rail				
FP A 200/180	Front plate (Aluminium)				
HFP 180	Front plate hinge series				
FP 22046	Wall fastening lug (4 pcs)				

