


PATCH CORDS - JUMPERS

STANDARD BANANA PLUG BOTH ENDS



AVAILABLE IN (12) RED AND
(10) BLACK


795-2060-XX 8 inches
795-2061-XX 12 inches
795-2062-XX 24 inches
795-2063-XX 36 inches
Specify Color

1st END - 40° angle standard banana plug.
Nickel plated brass body. Nickel plated beryllium copper spring. Polypropylene insulation.

WIRE - #18 AWG, stranded copper wire, PVC insulation.

2nd END - Same as 1st end

40° STANDARD BANANA PLUG TO CROSS PATCH PHONE TIP



AVAILABLE IN (12) RED AND
(10) BLACK


795-2090-XX 8 inches
795-2091-XX 12 inches
795-2092-XX 24 inches
795-2093-XX 36 inches
Specify Color

1st END - 40° angle standard banana plug.
Nickel plated brass body. Nickel plated beryllium copper spring. Polypropylene insulation.

WIRE - #18 AWG, stranded copper wire, PVC insulation.

2nd END - Cross patch phone tip. Nickel plated brass tip. Polypropylene insulation.

STANDARD BANANA PLUG TO MINIATURE BANANA PLUG



AVAILABLE IN (12) RED AND
(10) BLACK

795-2070-XX 8 inches
795-2071-XX 12 inches
795-2072-XX 24 inches
795-2073-XX 36 inches
Specify Color

1st END - 40° angle standard banana plug.
Nickel plated brass body. Nickel plated beryllium copper spring. Polypropylene insulation.

WIRE - #20 AWG, stranded copper wire, PVC insulation.

2nd END - 40° angle miniature banana plug.
Nickel plated brass body. Nickel plated beryllium copper spring. Polypropylene insulation.

INSULATED ALLIGATOR CLIP TO BANANA PLUG



AVAILABLE IN (12) RED AND
(10) BLACK


795-2300-XX 4 inches
795-2301-XX 8 inches
795-2302-XX 12 inches
795-2303-XX 24 inches
795-2304-XX 36 inches
795-2305-XX 48 inches
795-2306-XX 60 inches
Specify Color

1st END - Plated steel alligator clip with vinyl boot.

WIRE - #18 AWG, stranded copper wire, PVC insulation.

2nd END - Banana plug. Nickel plated brass body. Nickel plated beryllium copper spring. Butyrate insulation.

MINIATURE BANANA PLUG BOTH ENDS



AVAILABLE IN (12) RED AND
(10) BLACK

795-2065-XX 8 inches
795-2066-XX 12 inches
795-2067-XX 24 inches
795-2068-XX 36 inches
Specify Color

1st END - 40° angle miniature banana plug.
Nickel plated brass body. Nickel plated beryllium copper spring. Polypropylene insulation.

WIRE - #20 AWG, stranded copper wire, PVC insulation.

2nd END - Same as 1st end.

INSULATED SPADE LUG TO BANANA PLUG



AVAILABLE IN (12) RED AND
(10) BLACK

795-2330-XX 12 inches
795-2331-XX 24 inches
795-2332-XX 36 inches
795-2333-XX 48 inches
795-2334-XX 60 inches
Specify Color

1st END - Bright tin plated brass spade lug with butyrate insulation.

WIRE - #18 AWG, stranded copper wire, PVC insulation.

2nd END - Banana plug. Nickel plated brass body. Nickel plated beryllium copper spring. Butyrate insulation.

40° STANDARD BANANA PLUG TO STANDARD CROSS PATCH BANANA PLUG



AVAILABLE IN (12) RED AND
(10) BLACK

795-2080-XX 8 inches
795-2081-XX 12 inches
795-2082-XX 24 inches
795-2083-XX 36 inches
Specify Color

1st END - 40° angle standard banana plug.
Nickel plated brass body. Nickel plated beryllium copper spring. Polypropylene insulation.

WIRE - #18 AWG, stranded copper wire, PVC insulation.

2nd END - Cross patch stacking standard banana plug. Nickel plated brass body. Nickel plated beryllium copper spring.

SPADE LUG BOTH ENDS



AVAILABLE IN (12) RED AND
(10) BLACK

795-2100-XX 12 inches
795-2101-XX 24 inches
795-2102-XX 36 inches
795-2103-XX 48 inches
795-2104-XX 60 inches
Specify Color

1st END - Bright tin plated brass spade lug with butyrate handle

WIRE - #18 AWG, stranded copper wire, PVC insulation.

2nd END - Same as 1st end.



BLK	BRN	RED	ORN	YEL	GRN	BLU	PUR	GRY	WHT
10	11	12	13	14	15	16	17	18	19