



# RCA Phono Plugs

174-4356, 174-4357, 174-4358, 174-4359

**KOBI** CONN

RCA Phono Plugs

174-4356, 174-4357, 174-4358, 174-4359



## Dimensions: In.

SPECIFICATIONS	
Type:	RCA non shielded phono with cable protector
Net weight:	3.5g
Color I.D. ring:	red (174-4356), white (174-4357), yellow (174-4358), black (174-4359)
Rating:	34 AC/DC 2A
Insulation resistance:	100 mega $\Omega$ min. @ 500VDC
Contact resistance:	30 milli $\Omega$ Mac.
Dielectric strength:	250VAC for one minute
Handle:	polyethylene
Center terminal:	brass, nickel plated
Insulator:	ABS resin
Shield contact:	steel, nickel-plated
Center contact:	brass, nickel-plated

Date Last Revised: 4-19-05

Available from Mouser Electronics  
1-800-346-6873  
[www.mouser.com](http://www.mouser.com)

KC- 300549

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Kobiconn:

[174-4356](#) [174-4359](#) [174-4357](#) [174-4358](#)