

Dimensions

DIN 912


ISO 4762

BS 4168

Materials / Finishes:

Steel 12.9 high tensile / Self colour

Other materials and finishes available on request



d	M3	M4	M5	M6	M8	M10	M12	M14	M16	M18	M20	M22	M24	M27	M30	M36	M42
Max D*	5.5	7	8.5	10	13	16	18	21	24	27	30	33	36	40	45	54	63
Max H	3	4	5	6	8	10	12	14	16	18	20	22	24	27	30	36	42
S (key size)	2.5	3	4	5	6	8	10	12	14	14	17	17	19	19	22	27	32
t min	1.3	2	2.5	3	4	5	6	7	8	9	10	11	12	13.5	15.5	19	24

Preferred sizes - Steel

d	M3	M4	M5	M6	M8	M10	M12
L	5	TR					
	6	TR	TR				
	8	TR	TR	TR	TR		
	10	TR	TR	TR	TR	TR	
	12	TR	TR	TR	TR	TR	
	14	TR		TR	TR		
	16	TR	TR	TR	TR	TR	TR
	20	TR	TR	TR	TR	TR	TR
	25	TR	TR	TR	TR	TR	TR
	30	TR	TR	TR	TR	TR	TR
	35		TR	TR	TR	TR	TR
	40			TR	TR	TR	TR
	45			TR	TR	TR	TR
	50		TR	TR	TR	TR	TR
	55			TR	TR	TR	
	60			TR	TR	TR	TR
	65			TR	TR	TR	TR
	70			TR	TR	TR	TR
	75				TR	TR	TR
	80				TR	TR	TR
	90				TR		TR
	100						TR