

AULT SPECIFICATIONS

4-8VA Wall Plug Series

INPUT

Voltage	230 VAC
Line Frequency	50 Hz
Configuration	Euro Wall Plug, No Ground

OUTPUT

<i>Model Number</i>	<i>Rated Output Volts AC</i>	<i>Output Current Amps</i>	<i>Max VA</i>	<i>Agency Approvals</i>
A41-061333-A000G	6	1.33	8.0	EN60950
A41-071140-A000G	7	1.14	8.0	EN60950
A41-081000-A000G	8	1.00	8.0	EN60950
A41-090700-A000G	9	0.70	6.3	EN60742
A41-100800-A000G	10	0.80	8.0	EN60950
A41-110727-A000G	11	0.73	8.0	EN60950
A41-120667-A000G	12	0.67	8.0	EN60950
A41-140700-A000G	14	0.70	9.8	EN60742
A41-150533-A000G	15	0.53	8.0	EN60950
A41-160250-A000G	16	0.25	4.0	EN60742
A41-160500-A000G	16	0.50	8.0	EN60950
A41-180444-A000G	18	0.44	8.0	EN60950
A41-200400-A000G	20	0.40	8.0	EN60950
A41-220364-A000G	22	0.36	8.0	EN60950
A41-240333-A000G	24	0.33	8.0	EN60950

ELECTRICAL

Topology	Step Down AC/AC Transformer
Dielectric Withstand	3000 VAC primary-secondary
Protection	Current, Thermal or Energy Limiting
EMI	Complies with EMC Directives
CE	CE Compliant

ENVIRONMENTAL

Operating Temperature	0° to 40° C with no derating
Storage Temperature	-30° to +85° C
Relative Humidity	5% to 95% non-condensing
Altitude	0 - 10,000 feet
Cooling	Convectional non-vented case

MECHANICAL

Case and Dimensions	A41 - Euro Wall Plug 69 L X 52 W X 40 H (mm) 2.7 L X 2.0 W X 1.6 H (in)
Case Material	Black 94V1 Polycarbonate
Weight	9.6 ounces, 275 grams, (excluding cord)
Cord and Connectors	6 ft., 2 Conductor, 22-24 AWG, Ault #3 Connector Other connectors are also available

WARRANTY

1 Year