

NYS231LBG

3 pole 3.5 mm plug, with large cable outlet, black metal handle with gold plated contacts



Technical Information

Product	
Title	NYS231LBG
Electrical	
Dielectric strength	0.5 kVdc
Insulation resistance	≥ 1 GΩ
Rated current	depends on mated connector
Contact resistance	depends on mated connector
Mechanical	
Cable O.D.	6 mm
Lifetime	1000 mating cycles
Environmental	
Solderability	Complies with IEC 68-2-20
Temperature range	-25 °C to +70 °C