


ACP-1000/ 1000MB

1U Rackmount Chassis for SBC or ATX/MicroATX Motherboard



Features


- Easy-to-install disk drive bay to hold a slim optical disk drive and 3.5" disk drive
- Front-accessible USB and PS/2 ports for easy data transfer
- Reserved 9-pin D-Sub opening at rear
- ACP-1000BP supports up to two 64-bit full-length PCI cards
- ACP-1000MB supports full-length PCI or PCIe expansion cards via different riser card options
- Four cooling fans designed for optimizing the system's airflow




Specifications

		Front-accessible		Internal	
		1	-	-	1
Drive Bay	Slim Optical Disk Drive	1	-	-	1
	3.5"	1	-	-	1
Cooling	Fan	3 (10 CFM each)	Front-accessible	1 (10 CFM) / 1 (15 CFM)	Rear Panel
	Air Filter	Yes		-	
Front I/O Interface	USB	2			
	PS/2	1			
Miscellaneous	Rear Panel	Reserved one 9-pin D-Sub opening			
Environment		Operating		Non-Operating	
	Temperature	0 ~ 40° C (32 ~ 104° F)		-20 ~ 60° C (-4 ~ 140° F)	
	Humidity	10 ~ 85 % @ 40° C, non-condensing		10 ~ 95 % @ 40° C non-condensing	
	Vibration (5 ~ 500 Hz)	1 Grms		2 G	
	Shock	10 G (with 11 ms duration, half sine wave)		30 G	
Physical Characteristics	Dimensions (W x H x D)	BP: 480 x 44 x 497 mm (18.9" x 1.7" x 19.6") MB: 480 x 44 x 450 mm (18.9" x 1.7" x 17.7")			
	Weight	7.5 kg (16.5 lb) / 8 kg (17.6 lb)			

ACP-1000




ACP-1000MB




Dimensions

Unit: mm (inch)

ACP-1000



ACP-1000MB



Power Supply Options

Part Number	Specifications					
	Watt	Input	Output	Mini-load	Safety	MTBF
ACP-1000						
1757920000G (ATX, PFC)	200 W	AC 100 ~ 240 V (full-range)	+5 V @ 16 A, +3.3 V @ 14 A +12 V @ 9 A, -12 V @ 0.7 A -5 V @ 0.2 A, +5 Vsb @ 1.5 A	+5 V @ 2 A, +12 V @ 1 A -5 V @ 0.1 A, -12 V @ 0.1 A +5 Vsb @ 0.1 A	UL/TUV/CB/CCC	84,000 hours @ 25° C
1757918000G (ATX)	180 W	DC - 40 ~ 56 V	+5 V @ 20 A, +3.3 V @ 12 A +12 V @ 7 A, -12 V @ 1 A -5 V @ 0.5 A, +5 Vsb @ 1.5 A	+5 V @ 2 A, +12 V @ 1 A -5 V @ 0.1 A, -12 V @ 0.1 A +3.3 V @ 1 A, +5Vsb @ 0.1 A	UL/TUV/CB/CCC	100,000 hours @ 25° C
ACP-1000MB						
1757000005G (ATX, PFC)	200 W	AC 100 ~ 240 V (full-range)	+5 V @ 16 A, +3.3 V @ 14 A +12 V @ 9 A, -12 V @ 0.7 A -5 V @ 0.2 A, +5 Vsb @ 1.5 A	+5 V @ 2 A, +12 V @ 1 A -5 V @ 0.1 A, -12 V @ 0.1 A +5 Vsb @ 0.1 A	UL/TUV/CB/CCC	84,000 hours @ 25° C

Accessories

Part Number	Description
1750000242	Low profile P4 Socket 478 CPU cooler up to 2.5 GHz (0.13 micron)
1750000432	Low profile P4 Socket 478 CPU cooler up to 2.8 GHz (0.13 micron 70 W)
19991K0000	Filter 166 x 32 x 5 mm
96FDD-144-TE-B1	Black 3.5" FDD
96SCD-24X-I-OD-B	Black slim 24X CD-ROM
96SCOM-24X8X-TE-B1	Black slim 24X/8X/24X DVD RW-ROM

Riser Card Options

Part Number	Interface	Expansion Slot	Supported Motherboard
AIMB-R4104-01A1E	PCIe x4	One PCIe x4	AIMB-554/556
AIMB-RP10P-01A1E	PCI	One PCI	AIMB-740/742/744/750

Ordering Information

Part Number	Power Supply	Backplane / Motherboard	Regulation
ACP-1000BP-00XE	-	-	-
ACP-1000BP-20ZE	1757920000G	-	CE
ACP-1000MB0-20ZE	1757000005G	-	CE

* ACP-1000MB does not support for AIMB-763, 542, 562, 564 models due to the height of the audio connector is over 1U.



Rear 10-CFM cooling fan
Rear View of ACP-1000



Rear View of ACP-1000MB