




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
G	14		U4	REVISED PER ECO-11-004917	11MAR11	RK	HMR

D



STYLE I




STYLE III

B

8-321235-5	2.625	.860	NATURAL	CLEANED	I	LOOSE PC, BOX SPL	100	600	300
8-321235-1	2.625	.860	NATURAL	CLEANED		LOOSE PC, BOX	100	600	300
3-321235-0 2	2.625	1.151	BLACK	1	I	LOOSE PC	1000		
1-321235-4	2.438	.870	NATURAL	CLEANED	III	LOOSE PC	1000	600	300
1-321235-1	2.625	1.151	NATURAL	1	I	LOOSE PC	1000	600	300
1-321235-0	2.625	1.151	NATURAL	CLEANED		LOOSE PC	1000	600	300
321235	2.093	.860	NATURAL	CLEANED		LOOSE PC	1000	300	300
PART NO.	DIM 'A'	DIM 'B'	COLOR	FINISH	STYLE	PACKAGE TYPE	QTY	MAX VOLTAGE RATING	

- 1 TIN PLATE PER ASTM B545
- 2 PRELIMINARY - NOT FOR PRODUCTION

WIRE SPLICE		SEE TABLE	INSULATION: PVC COLOR: SEE TABLE BODY: BRASS (ASTM B-19) .032 THK FINISH: SEE TABLE					
DESCRIPTION		PART NO.	MATERIAL & FINISH					
THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 06OCT00	TE Connectivity					
DIMENSIONS: INCHES		CHK T. MICHIELUTTI 06OCT00						
	TOLERANCES, UNLESS OTHERWISE SPECIFIED:		APVD T. MICHIELUTTI 06OCT00	NAME SPLICE, RECEPTACLE, FASTON, .250 SERIES WIRE SIZE: 22-10				
	0 PLC ± -		PRODUCT SPEC					
	1 PLC ± -		-					
	2 PLC ± -		APPLICATION SPEC					
	3 PLC ± .008		-					
4 PLC ± -		-	SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO		
ANGLES ± -		WEIGHT	A2	00779	C-321235	-		
FINISH		SEE TABLE	CUSTOMER DRAWING					
			SCALE	NTS	SHEET	1 OF 1	REV	U4