

1420 Series Panel Enclosure

Non-Ventilated - NEMA 1

Commercial Enclosures



**Inner
Panel
Included**



Application

- Designed for indoor use to house controls, instruments and components which do not require oil-tight or dust-tight protection.

Standards

- UL 508 Type 1
- CSA Type 1
- **Complies with**
 - NEMA Type 1
 - IEC 60529, IP20

Construction

- Enclosure is formed and spot welded from 12 or 14 gauge steel.
- Removable 12 gauge inner panel is mounted to the rear of the enclosure on collar studs.
- Removable door is attached with slip hinges.
- To remove door, a tool is required to remove the #8 screw which captivates hinge.
- Door is fastened with a slotted 1/4 turn latch; doors 30" and higher are provided with two latches.
- A bonding stud is provided on the door and a grounding stud is provided in the box.
- Piano hinge on 12 gauge units

Finish

- Enclosure and door are finished in ANSI 61 gray powder coating.
- Inner panel is finished in white powder coating.

Accessories

- Additional inner panels...see page **438**
- Lock kit for NEMA 1 enclosures (Part No. **1427LKN1**)...see page **431**
- Louvered ventilating plates...see page **402**
- Window kits...see page **449**
- Padlock Adaptor...see page **435**

Panel Enclosures

Part No.	Mounting Centers			Panel Size						Ship Wt. lbs
	A	B	C	J	F	D	E	H	O	
1420B7	16	12	7	17.50	9.50	14	10	5.88	—	26
1420C7	20	16	7	21.50	10.00	18	14	5.88	—	39
1420D7	20	20	7	21.50	14.00	18	18	5.88	—	48
1420E7	24	20	7	25.50	14.00	22	18	5.88	—	53
1420F7	30	20	7	31.50	14.00	28	18	5.88	6.16	67
1420G7	30	24	7	31.50	18.00	28	22	5.88	6.16	79
1420H7	36	24	7	37.50	18.00	34	22	5.88	7.16	90
1420E9	24	20	9	25.50	14.00	22	18	7.88	—	60
1420EM9	24	24	9	25.50	18.00	22	22	7.88	—	71
1420G9	30	24	9	31.50	18.00	28	22	7.88	6.16	84

¹ 12 gauge construction

Technical references and CAD downloads available at www.hammondmfg.com


All dimensions in inches unless specified otherwise

1420 Series Panel Enclosure

Non-Ventilated - NEMA 1

Commercial Enclosures

Panel Enclosures



Part No.	A	B	C	Mounting Centers		Panel Size		H	O	Ship Wt. lbs
				J	F	D	E			
1420H9	36	24	9	37.50	18.00	34	22	7.88	7.16	98
1420P9	36	30	9	37.50	24.00	34	28	7.88	7.16	118
1420Q9	42	24	9	43.50	18.00	40	22	7.88	8.16	111
1420G12	30	24	12	31.50	18.00	28	22	10.88	6.16	92
1420P12	36	30	12	37.50	24.00	34	28	10.88	7.16	128
1420R12 ¹	42	30	12	43.50	24.00	40	28	10.88	8.16	142
1420S12 ¹	42	36	12	43.50	30.00	40	34	10.88	8.16	156
1420T12 ¹	48	36	12	49.50	30.00	46	34	10.88	9.16	214
1420G16	30	24	16	31.50	18.00	28	22	14.88	6.16	105
1420P16	36	30	16	37.50	24.00	34	28	14.88	7.16	144

¹ 12 gauge construction

Technical references and CAD downloads available at www.hammondmfg.com

All dimensions in inches unless specified otherwise

Quality Products. Service Excellence.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Hammond:](#)

[1420T12](#) [1420P16](#) [1420P12](#) [1420R12](#) [1420EM9](#) [1420B7](#) [1420F7](#) [1420H9](#) [1420D7](#) [1420H7](#) [1420P9](#) [1420G16](#)
[1420G12](#) [1420Q9](#) [1420C7](#) [1420G9](#) [1420G7](#) [1420E9](#) [1420E7](#) [1420S12](#)