




PVC, TFE & PE RG COAXIAL CABLES

UL CLASSIFIED* CL2 or CATV



BROADCAST & COMPUTER CABLE

NEC RATING	RG NO.	OLYMPIC NO.	AWG & STRANDING	COND. MAT'L.	INSULATION MATERIAL	THICKNESS	SHIELDS INNER	OUTER	JKT. MAT'L.	NOM. O.D.	JKT. COLOR	NOM. IMP. (OHMS)
	8/U	5237	#13 (7/21)	C	PE		CB	—	V	.415"	Black	50
	8A/U	5254	#13 (7/21)	C	PE		CB	—	NCV	.415"	Black	50
	9B/U	5264	#13 (7/21)	SC	PE		SC	SC	NCV	.430"	Black	50
	11/U	5238	#18 (7/26)	TC	PE		CB	—	V	.415"	Black	75
	11A/U	5261	#18 (7/26)	TC	PE		CB	—	NCV	.412"	Black	75
CL2	58/U	*5240 R	#20 (Solid)	C	PE		TC	—	V	.200"	Black	50
	58A/U	5259	#20 (19/32)	TC	PE		TC	—	V	.199"	Black	50
	58C/U	5262	#20 (19/32)	TC	PE		TC	—	NCV	.199"	Black	50
CL2	59/U	*6244 R	#22 (Solid)	CW	PE		CB	—	V	.242"	Black	75
	59B/U	5263	#23 (Solid)	CW	PE		CB	—	NCV	.242"	Black	75
CL2	62A/U	*6269 R	#22 (Solid)	CW	SSP		CB	—	V	.242"	Black	93
	62A/U	6268	#22 (Solid)	CW	SSP		CB	—	V	.260"	Black	93
	142B/U	53242	#18 (Solid)	SC	TFE		SC	SC	XFEP	.195"	Brown	50
	174/U	*5216	#26 (7/34)	CW	PE		TC	—	V	.105"	Black	50
	178B/U	53265	#30 (7/38)	SCW	TFE		SC	—	XFEP	.070"	Brown	50
	179B/U	53264	#30 (7/38)	SCW	TFE		SC	—	XFEP	.100"	Brown	75
	180B/U	53266	#30 (7/38)	SCW	TFE		SC	—	XFEP	.140"	Brown	95
	187A/U	53267	#30 (7/38)	SCW	TFE	.012	SC	—	F-TFE	.098"	White	75
	188A/U	53268	#26 (7/34)	SCW	TFE	.021	SC	—	F-TFE	.098"	White	50
	195A/U	53269	#30 (7/38)	SCW	TFE	.045	SC	—	F-TFE	.155"	White	95
	196A/U	53270	#30 (7/38)	SCW	TFE	.024	SC	—	F-TFE	.074"	White	50
CL2	213/U	5267	#13 (7/21)	C	PE	.020	CB	—	NCV	.405"	Black	50
	214/U	*5268	#13 (7/21)	SC	PE	.045	SC	SC	NCV	.425"	Black	50
	223/U	6273	#19 (Solid)	SC	PE	.011	SC	SC	NCV	.212"	Black	50
	316/U	53284	#26 (7/34)	SCW	TFE	—	SC	—	XFEP	.098"	Brown	50
Video		6174	#20 (Solid)	C	PE	.198	TC	TC	PE	.304"	Black	75

*UL1354 or UL1478



COAXIAL CABLES - CATV & CCTV

CATV	6/U	6245	#18 (Solid)	CW	FP		F	AB	V	.290"	Black	75
Direct Burial	6/U	6246 D	#18 (Solid)	CW	FP		F/F	AB	PE	.270"	Black	75
CL2	6/U	6246 R	#18 (Solid)	C	FP		F	TC	V	.270"	Black	75
CATV	6/U	6247	#18 (Solid)	CW	FP		QUAD		V	.300"	Black	75
CL2	59/U	6242	#20 (Solid)	C	FP		CB		V	.242"	Black	75
CATV	59/U	6291 R	#20 (Solid)	CW	FP		F	AB	V	.242"	Black	75
CATV	59/U	6293	#20 (Solid)	CW	FP		F	AB	V	.242"	Black	75
CATV	59/U	50837	#20 (Solid)	CW	FP		QUAD		V	.265"	Black	75
CATV	11/U	6294	#14 (Solid)	C	FP		F/F	AB	V	.405"	Black	75

C - Bare Copper
TC - Tinned Copper
SC - Silver Covered Copper
CW - Copper Covered Steel
SSFT - Semi-Solid FEP Teflon

PE - Solid Polyethylene
SSP - Semi-Solid Polyethylene
V - Polyvinylchloride - Type 1
NCV - Non-Contaminating PVC - Type 11A

SFT - Solid FEP Teflon
AB - Aluminum Braid
XFEP - Extruded FEP
FTFE - Fused TFE Tape
CB - Copper Braid

TFE - TFE Insulation
SCW - Silver Ctd. Copper Weld
FP - Foam Polyethylene
F - Foil
F/F - Al/Mylar/Al