


Dual Binding Post

164-19B2-EX

KOBICONN

Dual Binding Post



Dimensions: mm (in.)

SPECIFICATIONS

Rating:	10A 125V AC
Insulation Resistance:	DC 500V 100MΩ Min
Dielectric Strength:	AC 1000V 1 Minute
Temperature Range:	-10°C to +80°C
RoHS Compliant by Exemption	

MATERIALS

Insulation:	Nylon
Metal:	Nickel Plated Brass
Panel Thickness:	.5-4.5mm

Date Last Revised: 3/6/07

Available from Mouser Electronics
1-800-346-6873 / www.mouser.com

KC-301101

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.

164-19B2-EX