


Anna-50-3 series



Ordering number	C11608		
Description	C11608_Anna-50-3-W-OSL		
Family	Anna-50-3	FWHM	0 degrees
Type	Lens	Efficiency	-
LED	Oslon SSL 80	cd/lm	-
Color	Transparent	Gerber File	Available
Diameter	50 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		



4

3

2

1

4

3

2

1

Anna-3

Anna-4

Anna-5

Anna-6

Anna-7

Material: PMMA

Versions:

- Anna-3-S
- Anna-3-M
- Anna-3-W
- Anna-4-S
- Anna-4-M
- Anna-4-W
- Anna-5-S
- Anna-5-M
- Anna-5-W
- Anna-6-S
- Anna-6-M
- Anna-6-W
- Anna-7-S
- Anna-7-M
- Anna-7-W

Same top side
in all versions

Same location pin-circle
in all versions

Number of cones varies;
3, 4, 5, 6 and 7pcs
on bottom side depending
the version.

Same led-circle
in all versions

This drawing is our property.
It can't be reproduced
or communicated without
our written agreement.



L
T
F
F

e
e
i
i

N
n

d
h

DRAWING TITLE

Datasheet Anna50-series Lens

DRAWN BY

p

DATE

05.10.2010

CHECKED BY

t

k

DATE

03.08.2010

DESIGNED BY

hh

DATE

30.07.2010

SIZE

A4

DRAWING NUMBER

-

REV

1

SCALE

1:1

WEIGHT (g)

SHEET

1/1

D

A