



Double Coated Urethane Foam Tapes

4004 • 4008 • 4016 • 4026

4032 • 4052 • 4056 • 4085

Technical Data

April, 2009

Product Description

3M™ Double Coated Urethane Foam Tapes are conformable foams that offer high shear strength and are available with either a high temperature holding acrylic adhesive system or a rubber adhesive system for bonding to various types of surfaces for mounting, joining and holding.

Products

Note: The user is responsible for determining whether the tape is fit for a particular purpose and suitable for user's method of application.

3M™ Double Coated Urethane Foam Tape 4004	1/4 in.	(6.4 mm) thick
3M™ Double Coated Urethane Foam Tape 4008	1/8 in.	(3.2 mm) thick
3M™ Double Coated Urethane Foam Tape 4016	1/16 in.	(1.6 mm) thick
3M™ Double Coated Urethane Foam Tape 4026	1/16 in.	(1.6 mm) thick
3M™ Double Coated Urethane Foam Tape 4032	1/32 in.	(0.8 mm) thick
3M™ Double Coated Black Urethane Foam Tape 4052	1/32 in.	(0.8 mm) thick
3M™ Double Coated Black Urethane Foam Tape 4056	1/16 in.	(1.6 mm) thick
3M™ Double Coated Urethane Foam Tape 4085	0.045 in.	(1.1 mm) thick

3M™ Double Coated Urethane Foam Tapes

4004 • 4008 • 4016 • 4026 • 4032 • 4052 • 4056 • 4085

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

	Units	3M™ Double Coated Urethane Foam Tape			
		4004	4008	4016	4026
Adhesive Type:*		100	100	100	100
Adhesive Carrier:		Polyurethane Foam	Polyurethane Foam	Polyurethane Foam	Polyurethane Foam
Thickness: Nominal	inch (mm)	0.250 (6.4)	0.125 (3.2)	0.0625 (1.6)	0.0625 (1.6)
Thickness: Tolerance:	inch (mm)	0.215-0.285 (5.46-7.24)	0.110-0.150 (2.79-3.81)	0.045-0.080 (1.142-2.03)	0.045-0.080 (1.142-2.03)
Color:		Natural	Natural	Natural	Natural
Release Liner:	inch (mm)	0.003 (0.08)	0.003 (0.08)	0.003 (0.08)	0.003 (0.08)
Liner Color:		Green Plaid	Green Plaid	Green Plaid	Green Plaid
Approximate Density: (Foam Only)	lb/ft³ (kg/m³)	12 (190)	15 (240)	11 (175)	18 (290)
Standard Length:	yard (meter)	18 (16.5)	36 (32.9)	36 (32.9)	36 (32.9)
Maximum Length:	yard (meter)	25 (23)	50 (45.7)	100 (91)	100 (91)
Available Width:	inch (mm)	46 (1168)	46 (1168)	46 (1168)	46 (1168)
Normal Slitting Tolerance:	inch (mm)	± 1/32 (± 0.8)	± 1/32 (± 0.8)	± 1/32 (± 0.8)	± 1/32 (± 0.8)
Normal Tensile: ("T" Block) 1 in² (6.45 cm²) Jaw Speed 2 in/min (50 mm/min)	psi (kPa)	12 (85)	25 (170)	50 (345)	40 (275)
Static Shear:  Measured at various temperatures and gram loadings. (1/2 sq. in. overlap). Will hold listed weight for 100 hours.	gms	1000 500 500 250	1000 500 500 250	1500 1000 750 750	2000 1000 1000 750
Tensile Strength:	psi (kPa)	90 (620)	160 (1100)	140 (965)	180 (1240)
Elongation:	%	90	90	100	100
Temperature Resistance: Short Term (Minutes, Hours) Long Term (Days, Weeks)	°F (°C) °F (°C)	380 (193) 220 (104)	380 (193) 220 (104)	380 (193) 220 (104)	380 (193) 220 (104)
Solvent Resistance:		No apparent degradation when exposed to splash tests of most hydrocarbon solvents.			
UV Resistance:		No apparent degradation when exposed to 7 days in U.V. chamber.			
Cold Flex at -20°F (-30°C):		No cracking when flexed around a 1/4 in. (6.4 mm mandrel).			
Thermal Conductivity:	BTU/hr/°F/ft²/ft (watt/metre Kelvin)	0.036 (0.062)	0.036 (0.062)	0.036 (0.062)	0.036 (0.062)
Dielectric Strength:	volts/mil (volts/0.025 mm)	200-300 (200-300)	200-300 (200-300)	200-300 (200-300)	200-300 (200-300)

*3M™ Adhesive 100 is a firm acrylic pressure sensitive adhesive system. It features high ultimate bond strength, very good high temperature and solvent resistance and very high shear holding power. Bond strength increases substantially with natural aging.

3M™ Double Coated Urethane Foam Tapes

4004 • 4008 • 4016 • 4026 • 4032 • 4052 • 4056 • 4085

Typical Physical Properties

Note: The following technical information and data should be considered representative or typical only and should not be used for specification purposes.

	Units	3M™ Double Coated Urethane Foam Tape			
		4032	4052	4056	4085
Adhesive Type:*		100	100	100	740
Adhesive Carrier:		Polyurethane Foam	Polyurethane Foam	Polyurethane Foam	Polyurethane Foam
Thickness: Nominal	inch (mm)	0.031 (0.8)	0.031 (0.8)	0.0625 (1.6)	0.045 (1.2)
Thickness: Tolerance:	inch (mm)	0.025-0.040 (0.64-1.02)	0.025-0.040 (0.64-1.02)	0.045-0.080 (1.142-2.03)	0.039-0.054 (1.00-1.45)
Color:		Natural	Black	Black	Natural
Release Liner:	inch (mm)	0.003 (0.08)	0.003 (0.08)	0.003 (0.08)	0.003 (0.08)
Liner Color:		Green Plaid	Green Plaid	Green Plaid	Tan
Approximate Density: (Foam Only)	lb/ft ³ (kg/m ³)	20 (320)	14 (225)	11 (175)	22 (352)
Standard Length:	yard (meter)	72 (65.8)	72 (65.8)	36 (32.9)	72 (65.8)
Maximum Length:	yard (meter)	175 (160)	175 (160)	100 (91)	100 (91)
Available Width:	inch (mm)	46 (1168)	46 (1168)	46 (1168)	46 (1168)
Normal Slitting Tolerance:	inch (mm)	± 1/32 (± 0.8)	± 1/32 (± 0.8)	± 1/32 (± 0.8)	± 1/32 (± 0.8)
Normal Tensile: ("T" Block) 1 in ² (6.45 cm ²) Jaw Speed 2 in/min (50 mm/min)	psi (kPa)	60 (414)	75 (515)	50 (345)	45 (310)
Static Shear:  Measured at various temperatures and gram loadings. (1/2 sq. in. overlap). Will hold listed weight for 100 hours.	gms	2000 1500 1000 1050	1500 750 750 750	1500 1000 750 750	1000 250 — —
Tensile Strength:	psi (kPa)	240 (1655)	225 (1550)	140 (965)	140 (965)
Elongation:	%	90	110	100	100
Temperature Resistance: Short Term (Minutes, Hours) Long Term (Days, Weeks)	°F (°C) °F (°C)	380 (193) 220 (104)	380 (193) 220 (104)	380 (193) 220 (104)	200 (93) 125 (152)
Solvent Resistance:		No apparent degradation when exposed to splash tests of most hydrocarbon solvents.			
UV Resistance:		No apparent degradation when exposed to 7 days in U.V. chamber.			
Cold Flex at -20°F (-30°C):		No cracking when flexed around a 1/4 in. (6.4 mm mandrel).			
Thermal Conductivity:	BTU/hr/°F/ft ² /ft (watt/metre Kelvin)	0.036 (0.062)	0.036 (0.062)	0.036 (0.062)	0.036 (0.062)
Dielectric Strength:	volts/mil (volts/0.025 mm)	200-300 (200-300)	200-300 (200-300)	200-300 (200-300)	200-300 (200-300)

*3M™ Adhesive 100 is a firm acrylic pressure sensitive adhesive system. It features high ultimate bond strength, very good high temperature and solvent resistance and very high shear holding power. Bond strength increases substantially with natural aging.

3M™ Adhesive 740 is a medium-firm rubber-resin pressure sensitive adhesive system. It features good holding power and adhesion to a wide variety of surfaces including many low surface energy plastics such as polyethylene and polypropylene.

3M™ Double Coated Urethane Foam Tapes

4004 • 4008 • 4016 • 4026 • 4032 • 4052 • 4056 • 4085

Features

- The natural colored urethane foam tape products vary in color from white to light yellow. The color will change to light yellow upon exposure to sunlight (ultraviolet radiation). This color change is normal and does not affect tape performance.
- 3M™ Double Coated Urethane Foam Tape 4026 is available in roll form and die-cut pieces. Die-cut pieces of 3M tape 4026 is available in 3/4" or 1" squares, either individual pieces double lined with an extended liner on one side or in pads of 48 squares.
- 3M™ Double Coated Urethane Foam Tape 4085 combines conformability with high immediate adhesion to most plastics including ABS, polycarbonate, acrylic, polyethylene and polypropylene as well as metal and paint. 3M tape 4085 tears easily which makes it ideal for hand application.

Application Techniques

- Bond strength is dependent upon the amount of adhesive-to-surface contact developed. Firm application pressure helps develop better adhesive contact and improve bond strength.
 - To obtain optimum adhesion, the bonding surfaces must be clean, dry and well unified. Typical surface cleaning solvents are isopropyl alcohol* and water (rubbing alcohol) or heptane.
 - Ideal tape application temperature range is 70°F to 100°F (21°C to 38°C). Initial tape application to surfaces at temperatures below 50°F (10°C) is not recommended because the adhesive becomes too firm to adhere readily. However, once properly applied, low temperature holding is generally satisfactory.
- *Note:** Be sure to follow the manufacturer's precautions and directions for use when using solvents.

Application Ideas

The urethane foam tapes are generally ideal for interior applications or for exterior applications where the tape will be protected from the environment. The urethane foam is open cell.

- 3M™ Double Coated Urethane Foam Tape 4004 – Mount interior signs and nameplates
- 3M™ Double Coated Urethane Foam Tape 4008 – Bond acoustic panels to walls
- 3M™ Double Coated Urethane Foam Tape 4016 – Mount interior signs and nameplates
- 3M™ Double Coated Urethane Foam Tape 4026 – Mount air fresheners and soap dispensers
- 3M™ Double Coated Urethane Foam Tape 4032 – Attach wire clips to various surfaces
- 3M™ Double Coated Urethane Foam Tape 4052 – Bond window to microwave oven doors
Mount electrical channel to wall surfaces
- 3M™ Double Coated Urethane Foam Tape 4056 – Mount wall corner protectors
- 3M™ Double Coated Urethane Foam Tape 4085 – Attach wire clips
Attach air fresheners

3M™ Double Coated Urethane Foam Tapes

4004 • 4008 • 4016 • 4026 • 4032 • 4052 • 4056 • 4085

Storage

Store in original cartons at 70°F (21°C) and 50% relative humidity.

Shelf Life

To obtain best performance, use these products within 24 months from date of manufacture except 3M™ Double Coated Urethane Foam Tape 4085 which is 18 months from date of manufacture.

Certification/ Recognition

MSDS: 3M has not prepared MSDSs for these products which are not subject to the MSDS requirements of the Occupational Safety and Health Administration's Hazard Communication Standard, 29 C.F.R. 1910.1200(b)(6)(v). When used under reasonable conditions or in accordance with the 3M directions for use, these products should not present a health and safety hazard. However, use or processing of the products in a manner not in accordance with the directions for use may affect their performance and present potential health and safety hazards.

TSCA: These products are defined as articles under the Toxic Substances Control Act and therefore, are exempt from inventory listing requirements.

Technical Information

The technical information, recommendations and other statements contained in this document are based upon tests or experience that 3M believes are reliable, but the accuracy or completeness of such information is not guaranteed.

Product Use

Many factors beyond 3M's control and uniquely within user's knowledge and control can affect the use and performance of a 3M product in a particular application. Given the variety of factors that can affect the use and performance of a 3M product, user is solely responsible for evaluating the 3M product and determining whether it is fit for a particular purpose and suitable for user's method of application.

Warranty, Limited Remedy, and Disclaimer

Unless an additional warranty is specifically stated on the applicable 3M product packaging or product literature, 3M warrants that each 3M product meets the applicable 3M product specification at the time 3M ships the product. 3M MAKES NO OTHER WARRANTIES OR CONDITIONS, EXPRESS OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OR CONDITION OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR ANY IMPLIED WARRANTY OR CONDITION ARISING OUT OF A COURSE OF DEALING, CUSTOM OR USAGE OF TRADE. If the 3M product does not conform to this warranty, then the sole and exclusive remedy is, at 3M's option, replacement of the 3M product or refund of the purchase price.

Limitation of Liability

Except where prohibited by law, 3M will not be liable for any loss or damage arising from the 3M product, whether direct, indirect, special, incidental or consequential, regardless of the legal theory asserted, including warranty, contract, negligence or strict liability.

ISO 9001:2000

This Industrial Adhesives and Tapes Division product was manufactured under a 3M quality system registered to ISO 9001:2000 standards.



Industrial Adhesives and Tapes Division

3M Center, Building 225-3S-06
St. Paul, MN 55144-1000
800-362-3550 • 877-369-2923 (Fax)
www.3M.com/industrial



Recycled Paper
40% pre-consumer
10% post-consumer

3M is a trademark of 3M Company.
Printed in U.S.A.
©3M 2009 70-0705-7561-1 (4/09)