



Timers for mounting installation plan 25x32 Fixed timing, Positive output Part number 81503540




■ XXX

	Type	Code
81503540	Fixed timing, Positive output	81503540
81503710	Variable timing, 0,1 to 15 s Positive output	81503710
81506710	Variable timing, 0,1 to 15 s Negative output	81506710
81503720	Variable timing, Positive output 0,1 to 30 s	81503720
81506720	Variable timing Negative output 0.1 to 30 s	81506720


Symbol

Delay (s)	0,4
Operating pressure (bar)	2→8
Flow at 6 bars NI/min	170
Orifice diameter mm	2,7
Accuracy %	±5
Reset min. time S	<0,1
Operating temperature (° C)	-5 +50
Connection - Sub-base	■
Mechanical life (operations)	>10 ⁷
Weight (g)	106

Dimension Diagram : 81 503 540 - 81 506 540




: with positive output



Legend

Time

Curves : *** TRADUCTION MANQUANTE ***



N°	Legend
A	
B	