



## Home

Products |

[Philippines](#) > [Products & Services](#) > [Abrasives & Sandpaper](#) > [Products](#) > [Product Catalog](#)

### Home

#### Products

Coated and Bonded  
Surface Conditioning  
Abrasives  
Superabrasives  
Power Tools and Accessories

#### Resources


MSDS  
Promotion

#### Customer Service

Contact Us  
Where To Buy

[Product Catalog for Abrasives & Sandpaper](#) > [3M™ Aerospace Products and Sy and Tools](#) > [3M™ Scotchlok™ Terminals](#) > [3M™ Scotchlok™ Disconnects](#) > [3 Female Disconnects Nylon Fully Insulated Butted Seam](#) >

## 3M™ Scotchlok™ Female Disconnect Butted Seam MNU18-187DFIK, 22-18 A



[\[click to enlarge\]](#)

This terminal has a wire range of 22-18 AWG and has a

The disconnects are attached to mating part by tongue of dents and rolled edges on female part provides exce quick disconnect.

[« Close](#)

Products	Documentation
Product / 3M Id / UPC	3M™ Scotchlok™ Female Disconnect 187DFIK, 22-18 AWG 3M Id : 80-6100-6471-1 GTIN(UPC/EAN) : 0 00 54007 02370
Agency Approvals	UL and CSA
Barrel Inside Diameter	0.085 Inch
Barrel Length	0.25 Inch
Barrel Style	Butted
Brand	Scotchlok

<b>Conductor Sizes</b>	22 - 18 AWG
<b>CSA File Number</b>	LR22190
<b>Diameter (D)</b>	0.23 Inch
<b>Fastener Orientation</b>	Female
<b>Insulation Material</b>	Nylon
<b>Length (L)</b>	0.81 Inch
<b>Mates with Male Tab Width (W')</b>	0.187 Inch
<b>Maximum Insulation Outer Diameter</b>	0.145 Inch
<b>Packaging</b>	1000 per bulk box
<b>Pad Width</b>	0.187 Inch
<b>Terminal Style</b>	Fully Insulated
<b>Terminal Type</b>	Disconnect
<b>Thickness</b>	0.02 Inch
<b>UL File Number</b>	E70512
<b>Width (W)</b>	0.3 Inch

**3M:** [Careers](#) | [Investor Relations](#) | [MSDS Search](#) | [Advanced Search](#) | [Contact 3M](#)

[Legal Information](#) | [Privacy Policy](#)