



Mounted Points



- Pink abrasive mounted points
- Ideal for deburring, smoothing and general finishing applications
- The maximum recommended speeds given below are based on a maximum overhang of 133mm



| Shape | Shank<br>Ø | Size<br>x Length | Max.<br>Operating<br>Speed rpm | Order Code | Shape | Shank<br>Ø | Size<br>x Length | Max.<br>Operating<br>Speed rpm | Order Code |
|-------|------------|------------------|--------------------------------|------------|-------|------------|------------------|--------------------------------|------------|
| A3    | 6          | 25 x 70          | 16100                          | 700-9288   | B135  | 3          | 6 x 13           | 60000                          | 700-9409   |
| A4    | 6          | 32 x 32          | 29840                          | 700-9290   | W144  | 3          | 3 x 6            | 105000                         | 700-9410   |
| A5    | 6          | 19 x 28          | 45000                          | 700-9306   | W160  | 3          | 6 x 6            | 81370                          | 700-9422   |
| A11   | 6          | 22 x 50          | 19860                          | 700-9318   | W162  | 3          | 6 x 10           | 68400                          | 700-9434   |
| A12   | 6          | 18 x 32          | 48000                          | 700-9320   | W163  | 3          | 6 x 13           | 60000                          | 700-9446   |
| A24   | 6          | 6 x 19           | 76500                          | 700-9331   | W176  | 3          | 10 x 13          | 45370                          | 700-9458   |
| A25   | 6          | 25 x 25          | 35620                          | 700-9343   | W205  | 6          | 19 x 25          | 34500                          | 700-9471   |
| B52   | 3          | 10 x 19          | 43370                          | 700-9379   | W220  | 6          | 25 x 25          | 25500                          | 700-9483   |
| B81   | 3          | 19 x 5           | 47750                          | 700-9380   | W227  | 6          | 32 x 13          | 29840                          | 700-9495   |
| B97   | 3          | 3 x 10           | 105000                         | 700-9392   |       |            |                  |                                |            |

225154

| Shape | Order Code | Price Each |
|-------|------------|------------|
| A3    | 700-9288   |            |
| A4    | 700-9290   |            |
| A5    | 700-9306   |            |
| A11   | 700-9318   |            |
| A12   | 700-9320   |            |
| A24   | 700-9331   |            |
| A25   | 700-9343   |            |
| B52   | 700-9379   |            |
| B81   | 700-9380   |            |
| B97   | 700-9392   |            |
| B135  | 700-9409   |            |
| W144  | 700-9410   |            |
| W160  | 700-9422   |            |
| W162  | 700-9434   |            |
| W163  | 700-9446   |            |
| W176  | 700-9458   |            |
| W205  | 700-9471   |            |
| W220  | 700-9483   |            |
| W227  | 700-9495   |            |