



Wiha 3/8" Socket Accessories



602 65 3/8" Reversible Ratchet

45 tooth ratchet. DIN 3122 D - ISO 3315
hard chrome finish, polished head.

Item			
No.	Inch	mm	wt.
602 65	7.8	198	.63



602 66 3/8" Reversible Ratchet Varicat

32 tooth ratchet. DIN 3122 D - ISO 3315
Forged ratchet body, satin finish, nickel and hard chrome finish.
Spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
602 66	7.9	200	.54



602 67 3/8" Ratchet Push-Thru Type

30 tooth. DIN 3122 C - ISO 3315
hard chrome finish, polished head.

Item			
No.	Inch	mm	wt.
602 67	7.9	200	.54



602 68 3/8" Flexible Head Reversible Ratchet

60 tooth ratchet.
hard chrome finish, polished head.

Item			
No.	Inch	mm	wt.
602 68	10.04	255	.73



Provides ratcheting feature for non ratcheting tools. Use with, extension bars, speed brace, sliding T-handle and swivel handle.

602 49 3/8" Reversible Ratchet Unit

60 tooth ratchet. DIN 3122 A - ISO 3315
Hard chrome finish, satin finish with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
602 49	1.97	50	.44



602 3/8" Extension Bar

DIN 3123 B - ISO 3316

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
602 52	2.95	75	.14
602 51	4.92	125	.20
602 55	9.84	250	.36



602 3/8" Wobble Extension Hard chrome finish, fully polished with spring-loaded retaining ball.

Item				
No.	Inch	mm	wt.	
602 53	2.95	75	.13	
602 54	5.91	150	.23	
602 56	9.84	250	.36	



602 48 3/8" Speed Brace

DIN 3122 B - ISO 3315

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
602 48	11.97	304	.57



602 50 3/8" Sliding T-handle

DIN 3122 A - ISO 3315

Hard chrome finish, fully polished with spring-loaded retaining ball.

Item			
No.	Inch	mm	wt.
602 50	7.9	200	.35