




HONEYWELL
PART NUMBER

4



POS1 POS2 POS3

NUMBER OF POLES
(1=SP-SINGLE POLE, USES TERMINALS 1-2-3)
(2=DP-DOUBLE POLE, USES TERMINALS 1-2-3 AND 4-5-6)

TERMINAL STYLE

SRL

XX

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X

X



X

X

X

X

X

.250 WIDE QUICK
CONNECT TABS

MOUNTING HOLE

PANEL THICKNESS
(SNAP-IN BRACKET)
.030 MIN - .187 MAX
[.76] [4.75]

(A=AMBER, G=GREEN, R=RED, N=NONE)

(A=AMBER, G=GREEN, R=RED, N=NONE)

ILLUMINATION STYLE 9


CIRCUITRY 5

LAMP 7

LAMP 8

LED VOLTAGE
(2=6V, 3=12V, 4=24V)ACTUATOR COLOR
(B=BLACK, G=GRAY, R=RED, W=WHITE)BASE/BEZEL COLOR
(B=BLACK, G=GRAY, W=WHITE)LENS STYLE AND COLOR 7
8 = WHITE TRANSLUCENT BAR
9 = WHITE TRANSLUCENT SQUARE
N=NONELENS STYLE AND COLOR 8
8 = WHITE TRANSLUCENT BAR
9 = WHITE TRANSLUCENT SQUARE
N=NONEELECTRICAL RATINGS
AND APPROVALS10A 250VAC 1/2HP
15A 125VAC 1/2HP
UL, CSA

	CIRCUIT MADE WITH ROCKER IN 5		
	POSITION 3 (1&2, 4&5)	POSITION 2	POSITION 1 (2&3, 5&6)
1	ON	OFF	ON
2	OFF	NONE	ON
3	ON	NONE	ON
4	(OFF)	NONE	ON
5	(ON)	OFF	ON
6	OFF	NONE	(ON)
7	(ON)	OFF	(ON)
8	(ON)	NONE	ON



ILLUMINATION CIRCUIT DIAGRAMS 9

- 1 - OPERATING TEMPERATURE RANGE : -40°F TO +185°F
(-40°C TO +85°C)
2 - ELECTRICAL LIFE : 50,000 CYCLES MOMENTARY,
100,000 CYCLES MAINTAINED
3 - MECHANICAL LIFE : 150,000 CYCLES MIN
4 - SEE DIAGRAM FOR CATALOGING SCHEME
5 - PARENTHESIS DENOTE MOMENTARY ACTION
6 - SEALED TO IP68
7 - ABOVE TERMINALS 1 AND 4
8 - ABOVE TERMINALS 3 AND 6
9 - REFER TO CIRCUIT DIAGRAMS

DESIGN UNITS: INCH
TOLERANCES UNLESS NOTED:

NO PLACE	X	±	0.040
ONE PLACE	.X	±	0.030
TWO PLACE	.XX	±	0.015
THREE PLACE	.XXX	±	0.015
FOUR PLACE	.XXXX	±	0.0005
ANGLES	X	±	2

THIRD ANGLE PROJECTION

DRAWN TSG 14 JUL 05
CHECK - -THIS DRAWING COVERS A PROPRIETARY ITEM
AND IS THE PROPERTY OF HONEYWELL.
THIS DRAWING IS NOT TO BE COPIED OR USED
WITHOUT THE PERMISSION OF HONEYWELL.INTERPRET PER ASME Y14.5M-1994
OTHER HONEYWELL ENGINEERING
STANDARDS MAY APPLY

Pro/ENGINEER 2D

Honeywell

TITLE

SWITCH , ROCKER

SIZE	TYPE	DRAWING NAME	REV
B	I	SRL SERIES CHART 1	A
SCALE	-	SHEET	1 OF 1