

HBL1202 -- Hubbell-Pro Series Switches



Three Way, 15A 120/277V AC, Back and Side Wired, Almond

Product Specifications	
Product Type	 Toggle Switches
Switch Type	Double Pole
Switch Handle Positions	2
Switch Grade	Industrial
Amperage	15A
Voltage	120/277V AC
Color	 Brown
Wiring Style	Back and Side Wired
Operating Temperatures	Max Continuous- 75 Degrees C, Minimum- -40 Without Impact
Listing and Certifications	Listed to Standard UL 20, CSA Certified, Meets NEMA WD1
Weight in LBs	0.2
UPC Number	783585430164
Link to Drawing Library	Click here for Library
Link to PDF Catalog	Click here for Catalog

