

BRADY B-499 THERMAL TRANSFER / DOT MATRIX PRINTABLE NYLON CLOTH LABEL

TDS No. B-499

Effective Date: 10/05/2022

Description:

GENERAL

Print Technology: Thermal transfer

Material Type: Polyamide coated nylon cloth

Finish: Matte white

Adhesive: Permanent acrylic

APPLICATIONS

Wiremarking and general labeling applications

B-499 is not recommended for outdoor use.

RECOMMENDED RIBBONS

Thermal Transfer Ribbons

Brady Series R4300

Brady Series R4900

Brady Series R6000 Halogen Free

Brady Series R6200

Brady Series R4500 colored (red, blue and green)

Dot Matrix Ribbons

Brady Series R5000

REGULATORY/AGENCY APPROVALS

UL: B-499 is a UL Recognized Component to UL969 Labelling and Marking Standard when printed with Brady Series R4300, R4900, R6000 Halogen Free thermal transfer ribbons and Brady Series R5000 dot matrix ribbon. See UL file MH17154 for specific details. UL information can be accessed online at UL.com. Search in the Certifications area.

CSA: B-499 is CSA Accepted to C22.2 No.0.15-95 Adhesive Labels Standard when printed with Brady Series R4300 thermal transfer ribbon. See CSA file 041833 for specific details. CSA information can be accessed online at

<https://www.csagroup.org/testing-certification/product-listing/>

For information on the Weee-RoHS compliance status for a Brady Product go to one of the following websites:

In Canada: www.bradycanada.ca/weee-rohs

In Europe: www.bradyeurope.com/rohs

In Japan: www.brady.co.jp/products/labelsuse/rohs

All other regions: www.bradyid.com/weee-rohs

SPECIAL FEATURES

DIN VDE 0472 Part 815: Brady B-499 meets requirements of a halogen-free material per DIN VDE 0472 part 815. (Statement based on review of product construction and confirmation halogen content test run at an independent test laboratory)

Details:

PHYSICAL PROPERTIES	TEST METHODS	AVERAGE RESULTS
Thickness	ASTM D 1000 -Substrate -Adhesive -Total (excluding liner)	0.0045 inch (0.115 mm) 0.0020 inch (0.051 mm) 0.0065 inch (0.166 mm)
Adhesion to: -Stainless Steel	ASTM D 1000 20 minute dwell 24 hour dwell	45 oz/inch (50 N/100 mm) 80 oz/inch (88 N/100 mm)
-Textured ABS	20 minute dwell 24 hour dwell	35 oz/inch (39 N/100 mm) 40 oz/inch (44 N/100 mm)
-Polypropylene	20 minute dwell 24 hour dwell	24 oz/inch (26 N/100 mm) 24 oz/inch (26 N/100 mm)

Tack	ASTM D 2979 Polyken™ Probe Tack (1 second dwell, 1cm/sec separation)	29 oz (900 grams)
Drop Shear	PSTC-7 (except use 1/2" x 1" sample)	9 hours
Tensile Strength and Elongation	ASTM D 1000 -Machine	80 lb/in (1400 N/100 mm), 50%

Performance properties tested on B-499 printed with the Brady Series R4300, R4900, R6000 Halogen Free and R6200 thermal transfer ribbons and the Brady Series R5000 dot matrix ribbon. Printed samples of B-499 were laminated to aluminum and allowed to dwell 24 hours before exposure to the indicated environmental conditions. Unless noted, results are the same for all ribbons tested.

PERFORMANCE PROPERTIES	TEST METHOD	TYPICAL RESULTS
Short Term High Service Temperature	5 minutes at 293°F (145°C)	No visible effect to label at 145°C, slight shrinkage at 180°C but label still functional
Long Term High Service Temperature	30 days at 193°F (90°C)	No visible effect to label at 90°C, slight discoloration at 110°C but label still functional, at 120°C label is severely discolored
Low Service Temperature	30 days at -40°F (-40°C)	No visible effect
Weatherability*	ASTM G155, Cycle 1 30 days in Xenon Arc Weatherometer	Material wrinkled and embrittled
Humidity Resistance	30 days at 100°F, 95% R.H.	No visible effect
UV Light Resistance	30 days in UV Sunlighter™ 100	No visible effect
Abrasion Resistance	Taber Abraser, CS-10 grinding wheels, 500 g/arm (Fed. Std. 191A, Method 5306)	Print still legible at: 150 cycles with R4300, R4900, R6000 Halogen Free, R6200, and R5000 ribbons

*B-499 is not recommended for long-term outdoor use.

PERFORMANCE PROPERTY	CHEMICAL RESISTANCE
----------------------	---------------------

Samples printed with the Brady Series R5000 ribbon. Samples wrapped around a 12 AWG, TFE jacketed wire and allowed to dwell 24 hours prior to test. Test was conducted at room temperature except where noted. Testing consisted of 5 cycles of 10 minute immersions in the specified test fluid followed by a 30 minute recovery period. After final immersion, samples rubbed 10 times with cotton swab saturated with test fluid.

CHEMICAL REAGENT	SUBJECTIVE OBSERVATION OF VISUAL CHANGE	
	EFFECT TO LABEL STOCK	R5000 DOT MATRIX RIBBON
Methyl Ethyl Ketone	Complete unwrap	No visible effect
1,1,1-Trichloroethane	Complete unwrap	No visible effect
Isopropyl Alcohol	Complete unwrap	No visible effect
Mineral Spirits	Complete unwrap	No visible effect
SAE 20 WT Oil at 70°C	No unwrap, label stained tan	No visible effect
Mil 5606 Oil	Slight unwrap, label stained red	No visible effect
Gasoline	Adhesive failure, label discoloration	No visible effect
Rust Veto® 342	Moderate unwrap, label discoloration	No visible effect
Deionized Water	No visible effect	No visible effect
3% Alconox® Detergent	No visible effect	No visible effect w/o rub, moderate print removal after rub
10% Sodium Hydroxide Solution	Complete unwrap	No visible effect
10% Sulfuric Acid Solution	No visible effect	No visible effect
Northwoods™ Buzz Saw Degreaser	Complete unwrap	No visible effect w/o rub, slight print removal after rub
Speedi Kut Cutting Oil 332	No unwrap, label stained red	No visible effect
5% Salt Solution	No visible effect	No visible effect

Samples printed with the Brady Series R4300, R4900, R6000 Halogen Free and R6200 thermal transfer ribbons. Samples laminated to aluminum panels and allowed to dwell 24 hours prior to test. Test performed at room temperature except where noted. Testing consisted of 5 cycles of 10 minute immersions in the specified test fluid followed by a 30 minute recovery period.

After final immersion, samples rubbed 10 times with cotton swab saturated with test fluid.

CHEMICAL REAGENT	SUBJECTIVE OBSERVATION OF VISUAL CHANGE			
	R4300 THERMAL TRANSFER RIBBON	R4900 THERMAL TRANSFER RIBBON	R6000 Halogen Free THERMAL TRANSFER RIBBON	R6200 THERMAL TRANSFER RIBBON
Methyl Ethyl Ketone	No visible effect w/o rub, slight print removal after rub	No visible effect w/o rub, slight print removal after rub	No visible effect w/o rub, moderate print smear after rub	No visible effect w/o rub, slight print smear after rub
1,1,1-Trichloroethane	No visible effect	No visible effect	Obsolete	No visible effect
Isopropyl Alcohol	No visible effect w/o rub, moderate print removal after rub	No visible effect w/o rub, complete print removal after rub	No visible effect w/o rub, slight print removal after rub	No visible effect w/o rub, moderate print removal after rub
Mineral Spirits	No visible effect w/o rub, slight print removal after rub	No visible effect	No visible effect	No visible effect
SAE 20 WT Oil at 70°C	No visible effect w/o rub, severe print removal after rub	No visible effect	No visible effect	No visible effect
Mil 5606 Oil	No visible effect w/o rub, slight print removal after rub	No visible effect	No visible effect	No visible effect
Gasoline	No visible effect	No visible effect	No visible effect	No visible effect w/o rub, slight print smear after rub
Rust Veto® 342	No visible effect w/o rub, severe print removal after rub	No visible effect w/o rub, moderate print removal after rub	No visible effect	No visible effect
Deionized Water	No visible effect w/o rub, moderate print smear after rub	No visible effect w/o rub, severe print removal after rub	No visible effect	No visible effect w/o rub, slight print removal after rub
3% Alconox® Detergent	No visible effect w/o rub, slight print removal after rub	No visible effect w/o rub, severe print removal after rub	No visible effect w/o rub, slight print removal after rub	No visible effect w/o rub, slight print removal after rub
10% Sodium Hydroxide Solution	No visible effect	No visible effect	No visible effect w/o rub, slight print smear after rub	No visible effect
10% Sulfuric Acid Solution	No visible effect w/o rub, moderate smear after rub	No visible effect w/o rub, moderate print removal after rub	No visible effect w/o rub, slight print removal after rub	No visible effect w/o rub, slight print removal after rub
Northwoods™ Buzz Saw Degreaser	No visible effect w/o rub, moderate print removal after rub	No visible effect w/o rub, print illegible after rub	No visible effect w/o rub, moderate print removal after rub	No visible effect w/o rub, slight print removal after rub
Speedi Kut Cutting Oil 332	No visible effect	No visible effect	No visible effect	No visible effect
5% Salt Solution	No visible effect	No visible effect	No visible effect	No visible effect w/o rub, slight print removal after rub

Shelf Life:

Shelf life is two years from the date of receipt for this product as long as this product is stored in its original packaging in an environment below 80° F (27° C) and 60% RH. It remains the responsibility of the user to assess the risk of using this product. We encourage customers to develop testing protocols that will qualify a product's fitness for use in their actual applications.

Trademarks:

Alconox® is a registered trademark of Alconox Co.
I.D. Pro® is a registered trademark of Brady Worldwide, Inc.
Northwoods™ is a trademark of the Superior Chemical Corporation.
Polyken™ is a trademark of Testing Machines Inc.
Rust Veto® is a registered trademark of the E.F. Houghton & Co.
Sunlighter™ is a trademark of the Test Lab Apparatus Company
ASTM: American Society for Testing and Materials (U.S.A.)
SAE: Society of Automotive Engineers (U.S.A.)
CSA: Canadian Standards Association UL:
Underwriters Laboratories Inc. (U.S.A.)
All S.I. Units (metric) are mathematically derived from the U.S. Conventional Units.

Note: All values shown are averages and should not be used for specification purposes.

Test data and test results contained in this document are for general information only and shall not be relied upon by Brady customers for designs and specifications, or be relied on as meeting specified performance criteria. Customers desiring to develop specifications or performance criteria for specific product applications should contact Brady for further information.

Product compliance information is based upon information provided by suppliers of the raw materials used by Brady to manufacture this product or based on results of testing using recognized analytical methods performed by a third party, independent laboratory. As such, Brady makes no independent representations or warranties, express or implied, and assumes no liability in connection with the use of this information.

WARRANTY

Brady products are sold with the understanding that the buyers will test them in actual use and determine for themselves their adaptability to their intended uses. Brady warrants to the buyers that its products are free from defects in material and workmanship, but limits its obligation under this warranty to replacement of the product shown to Brady's satisfaction to have been defective at the time Brady sold it. This warranty does not extend to any persons obtaining the product from the buyers. This warranty is in lieu of any other warranty, express or implied, including, but not limited to, any implied warranty of merchantability or fitness for a particular purpose, and of any other obligations or liability on Brady's part. Under no circumstances will Brady be liable for any loss, damage, expense, or consequential damages of any kind arising in connection with the use, or inability to use, Brady's products.

Copyright 2022 Brady Worldwide, Inc. | All Rights Reserved
Material may not be reproduced or distributed in any form without written permission.

Brady North America | 6555 W. Good Hope Rd | Milwaukee, WI 53223 | USA | Tel: 414-358-6600 | Fax: 800-292-2289