

Mini Pocket MultiMeter


Autoranging with 10 functions including Frequency, Capacitance, and DutyCycle
With Diode Test and Continuity Beeper.

Features:

- Large high contrast 4000 count LCD display
- Auto Power off to conserve battery life
- Autoranging with Relative and Data Hold
- Diode Test and Continuity Beeper
- Built-in storage compartment for integrated test leads
- Protective rubber holster provides extra protection on the meter
- Over-range and low battery indication
- Complete with test leads, protective holster, one CR 2032 button battery and carrying case

Applications:

- Home wiring projects
- Testing electrical systems on cars and boats
- Hobby projects



Integrated test leads for accurate readings



Includes holster and pouch carrying case for added protection

Specifications	Range	Max. Resolution	Basic Accuracy (%rdg+digits)
DC Voltage	500V	0.1mV	±(1.3% + 3d)
AC Voltage	500V	1mV	±(2.3% + 5d)
DC Current	400.0mA	0.01mA	±(2.0% + 5d)
AC Current	400.0mA	0.01mA	±(2.5% + 10d)
Resistance	400 to 40MΩ	0.1Ω	±(2.0% + 5d)
Capacitance	200μF	0.001nF	±(3.0% + 15d)
Frequency	9Hz to 10MHz	0.001Hz	±(2% + 5d)
Duty Cycle	0.1% to 99.9%	0.1%	±(2% + 5d)
Diode Test	Test Current at 0.6mA		
Continuity Test	Audible beep <60Ω		
Dimensions	4.25 x 2.2 x 0.5" (108 x 56 x 11.5mm)		
Weight	1.7oz (50g)		

Ordering Information:

DM110Mini Pocket MultiMeter

