

PRODUCT NUMBER

71600-YXXXLF

LEAD FREE, SEE NOTE 6

COLOR OPTION, SEE NOTE 1

TOTAL NB OF POSITION 04 TO 64
SEE SHEET 2

OPTIONAL STRAIN RELIEF
SEE SHEET 2

TRIANGLE INDICATES
POSITION 1
NOTE 5

LEFT POLARIZING
NOTE 5

CENTRAL KEY
NOTE 5

RIGHT POLARIZING
NOTE 5

NOTES:

1 - HOUSING MATERIAL : GLASS FILLED
THERMOPLASTIC. UL94V-0 COLOR: GREY

= STANDARD COLOR GREY
B = OPTION COLOR BLACK

2 - PIN MATERIAL : PHOSPHOR BRONZE

3 - PRODUCT PACKAGED IN TUBES.

4 - TO DETERMINE DIMENSIONS :
N = NUMBER OF POSITIONS PER ROW
EXAMPLE : 8 POS N x 2.54 = 20.32mm

5 - 2x5, 2x6, 2x7 HAVE NO LEFT POLARIZING SLOT.

- 2x2, 2x3 WITH CENTRAL KEY HAVE NO TRIANGLE, NO
LEFT AND RIGHT POLARIZING SLOT.



- 2x2 WITHOUT CENTRAL KEY HAS NO LEFT AND RIGHT
POLARIZING SLOT.

- 2x3, 2x4 WITHOUT CENTRAL KEY HAVE NO LEFT POLARIZING SLOT

- 2x4 WITH CENTRAL KEY HAVE NO LEFT AND RIGHT POLARIZING SLOT

6 - THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATIONS AS PER GS-22-008.


PACKAGING SPECIFICATION AS PER GS-14-920.




mat'l. code SEE NOTES				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101	projection mm	product family 2.54MM IDC	
lfr	ecn no	dr	date	tolerances unless otherwise specified				title	
AP	F12-0046	LMU	12.04.25	angles	linear	X.X ±0.3		QUICKIE III FEM	
AR	B-17851	LMU	14.06.05			X.XX ±0.13		0.76µm Au	
AS	F-26816	LMU	17.06.06			X.XXX ±0.05	scale 5:1	dwg no	
				dr	D.LE	01.01.24		sheet 1 of 2 size	
AL	F06-0270	LMU	06.09.12	engr	P.NZ	01.01.24		71600	
AM	F06-0274	LMU	06.09.25	chr	JF.N	01.01.24		A3	
AN	F09-0233	LMU	09.12.15	appd	P.NZ	01.01.24		type	
sheet	revision	AS	AG					CUSTOMER Drawing	
index	sheet	1	2						

STRAIN RELIEF OPTION AVAILABILITY	Nbr OF POSITIONS
1/6	04
0/1/2/3/6	06
0/1/2/3/6	08
0/1/2/3/6	10
0/1/2/3/6	14
0/1/2/3/6	16
0/1/2/3/6	18
0/1/2/3/6	20
0/1/3	24
0/1/2/3/6	26
0/1/2/3/6	30
0/1/2/3/6	34
0/1/2/3/6	40
0/1/2/3/6	50
0/1/2/3/6	60
0/1/2/3/6	64
PLATING 0.76µm GOLD ON CONTACT AREA 1.27 µm Ni REMAINDER OF PRODUCT	


624
304
204 / 224
004
DASHES NOT AVAILABLE




WITHOUT STRAIN RELIEF




WITH LOW PROFILE STRAIN RELIEF




WITH STANDARD STRAIN RELIEF




WITH LATCHING STRAIN RELIEF



LOW PROFILE STRAIN RELIEF



STANDARD STRAIN RELIEF



LATCHING STRAIN RELIEF FOR SLIM HEADER

71600-6YY(B)LF	●					●
71600-3YY(B)LF		●	●			
71600-2YY(B)LF	●				●	
71600-1YY(B)LF	●			●		
71600-0YY(B)LF	●		●			
PRODUCT NUMBER	WITH CENTRAL KEY	WITHOUT	STANDARD	WITHOUT	LOW PROFILE	LATCHING

mat'l. code	surface	tolerance	projection	product family
	ISO 1302	ISO 406 ISO 1101		QUICKIE
ltr	ecn no	dr	date	title
AF	B-17851	LMU	14.06.05	IDC RECEPT
AG	F-26816	LMU	17.06.06	DR
AB	F03019	DLE	03.01.23	
AC	F05-0180	LMU	05.04.22	
AD	F06-0270	LMU	06.09.12	
AE	F06-0274	LMU	06.09.25	
sheet index	revision sheet			



dwg no	sheet 2 of - size
71600	A3
type	CUSTOMER Drawing