


Dimensions: mm (in.)

**Electrical Specifications:**

- Life: 1000 cycles
- Non-Switching Rating: 100mA/50VDC
- Switching Rating: 25mA/24VDC
- Contact Resistance: 100mΩ max. at initial
- Insulation Resistance: 100MΩ min. at (500VDC)
- Dielectric Strength: 300VAC/1minute

Mechanical Specifications:

- Life: 1000 cycles
- Operation Force: 500gf
- Stroke: 0.6mm
- Operating Temperature: -40°C to +85°C
- Storage Temperature: -40°C to +85°C

Note:

- RoHS Compliant

Mouser Stock No.	No. of Pos.	Dimensions A mm (in.)
106-HNF2-EV	2	3.77 (.148)
106-HNF4-EV	4	6.31 (.248)
106-HNF6-EV	6	8.85 (.348)
106-HNF8-EV	8	11.39 (.448)
106-HNF1-EV	10	13.93 (.548)

Dip Switches

106-HNF1-EV, 106-HNF2-EV, 106-HNF4-EV,
106-HNF6-EV, 106-HNF8-EV

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mountain Switch:

[106-HNF1-EV](#) [106-HNF6-EV](#) [106-HNF2-EV](#) [106-HNF4-EV](#) [106-HNF8-EV](#)