

Technical drawing of a cable assembly with dimensions and labels:

- H REF. NOMINAL HOLE DIAMETER $+0.010 (.25) / -0.005 (.13)$**
- J REF. $\pm 0.030 (.76)$**
- G REF.**
- C REF.**
- E**
- B $\pm 0.01 (.25)$**
- F REF.**
- D REF.**
- A $\pm 0.01 (.25)$**

PANDUIT PART NO.*	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	G in (mm)	H in (mm)	J in (mm)	MAX. PANEL THICKNESS in (mm)	MIN. LOOP TENSILE lbs (N)	CROSS SECTION	WEIGHT 100 pcs lbs (g)
	MIN. in (mm)	MAX. in (mm)													
PRWP1S	.06 (1.5)	1.00 (25.4)	.052 (1.3)	.190 (4.8)	.300 (7.6)	.370 (9.4)	.320 (8.1)	5.2 (132)	.33 (8.4)	.250 (6.4)	.74 (18.8)	.105 (2.7)	50 (222)	STANDARD	.29 (132)
PRWP1.5S	.06 (1.5)	1.50 (38.1)	.052 (1.3)	.190 (4.8)	.300 (7.6)	.370 (9.4)	.320 (8.1)	6.8 (173)	.33 (8.4)	.250 (6.4)	.74 (18.8)	.105 (2.7)	50 (222)	STANDARD	.34 (154)
PRWP2S	.06 (1.5)	1.75 (44.5)	.052 (1.3)	.190 (4.8)	.300 (7.6)	.370 (9.4)	.320 (8.1)	7.8 (198)	.33 (8.4)	.250 (6.4)	.74 (18.8)	.105 (2.7)	50 (222)	STANDARD	.37 (168)

*1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE & PART COLOR.
2) RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES INC.

PANDUIT CORP. TINLEY PARK, ILLINOIS
RELEASING WING PUSH MOUNT TIE
PRWP

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X)± .1(2.5) (.XXX)± .020(.51)
(.XX)± .02(.5) ANGLES± ---

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
WKS

DATE	3-31-87
------	---------

CHK'D	HVP
-------	-----

MAT'L:

NYLON 6/6

SCALE	NONE
-------	------

DRAWING NO.
SS-17556

DWG
A
SIZE

[illegible]