





NOTES:
1. INK RIBBON ASSEMBLY, SEE NO. A85169.
2. MILLIMETER ARE IN [].

PANDUIT PART NO.	A	B	C	E	LABELS/ROLL
N100X150CBC	1.125	1.000 [25.4]	1.500 [38.1]	0.25 [6.35]	75

											CAD FILENAME/LAYERS I00743MK_AC10426_N100X150CBC_00.PRT					
											PANDUIT CORP TINLEY PARK, ILLINOIS CUSTOMER DRAWING LS8 NON-LAMINATING LABELS N100X150CBC					
											UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .031 (,.XXX) ± .005 (.XX) ± .015 ANGLES ± 5 °		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION			
											DRAWN BY RVU	MAT'L: GMC-T39WS-TA GM60-80LB-VC		SCALE NTS		
											DATE 6-20-06			DRAWING NO. C10426		DWG B
											CHK'D			SIZE		
0	6-20-06	RVU	DWY	RELEASE TO PRODUCTION.				4503	R							
REV	DATE	BY	CHK	DESCRIPTION				ECN	-	R	CUST	SUP				