

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [130103-0054](#)
Status: **Active**
Overview: [Hand Lamps](#)
Description: Watertite® Wet Location Incandescent Hand Lamp 100W with Screw Release
Grounded Insulated Reflector Guard, Cord Type 16/3 SOOW 30.48m (100.0') Cord
Length

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

[Product Literature \(PDF\)](#)

Agency Certification

CSA LR85374

General

Product Family Portable Lighting
Series [130103](#)
NEMA Configuration NEMA 5-15
NEMA Rating NEMA 4X
Outlet None
Overview [Hand Lamps](#)
Product Literature Order No 987650-8053
Product Name Watertite®
Type Hand Lamps
UPC 78678835594
Woodhead Yes

Physical

Cord Length - Primary 30.48m (100.0')
Cord Length - Secondary N/A
Depth 120.65mm (4.750")
Duty Wet Location
Guard Included No
Guard Type Vinyl Coated
Height 457.20mm (18.000")
Length N/A
Material - Globe Tempered Glass
Material - Guard #8 Gauge Zinc-plated Steel
Mounting Style Hand Held
Net Weight 2.960/kg
Packaging Type Carton
Socket Construction N/A

Electrical

Bulb Type Incandescent
Cord Type - Primary 16/3 SOOW
Lamp Type A21
Lamp Wattage - Maximum 100W
Lumens 1000
On/Off Switch No
Voltage (Fixture) - Maximum 120V AC

Material Info

Old Part Number 1203RID163



image - Reference only

EU RoHS

ELV and RoHS

Compliant

REACH SVHC

Not Reviewed

Low-Halogen Status

Not Reviewed

China RoHS



**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
For a multiple part number RoHS Certificate of
Compliance, [click here](#)

Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[130103Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION